

6

5

4

3

2

1

| REVISION | | | | | |
|----------|-----|-----------------|------------|------------|------------|
| ZONE | REV | DESCRIPTION | DATE | CHANGED BY | APPROVED |
| | A | INITIAL RELEASE | 12/06/2023 | BZHANG | GUTTADAURO |

F

F

E

E

D

D

C



C

B

B

A

A



NOTES:

- 1.LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
- 2.PLUG CONFORMS TO TIA-1096.
- 3.CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
- 4.CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

| PART NUMBER | LENGTH METERS[FEET] |
|----------------|---------------------|
| TRD795RED-05M | 0.5[1.64] |
| TRD795RED-1M | 1.0[3.28] |
| TRD795RED-2M | 2.0[6.56] |
| TRD795RED-3M | 3.0[9.84] |
| TRD795RED-5M | 5.0[16.41] |
| TRD795RED-7.5M | 7.5[24.61] |
| TRD795RED-10M | 10.0[32.81] |
| TRD795RED-15M | 15.0[49.21] |

| | | | | | |
|--|-----------|--|-----------|---|-------|
| UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS | | <p>L-com an INFINIT@ brand</p> <p>Website: www.L-com.com Phone: 1.800.341.5266 1.978.682.6936</p> | | <p>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</p> | |
| TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [0.5] ANGLES ± 1° .XXX = ±.005 [0.13] | | | | SCALE | SHEET |
| CABLE LENGTH TOLERANCES UNLESS OTHERWISE SPECIFIED: ≤12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 | | NONE 1 OF 1 | | | |
| DESCRIPTION | | | | CA,CAT7 S/FTP RJ45 TO RJ45 PVC JKT,RED | |
| SIZE | CAGE CODE | DRAWN BY | ITEM NO. | REV | |
| A | 43321 | BZHANG | TRD795RED | A | |

6

5

4

3

2

1