



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/21/2021	D.GUTTADAURO



PART NUMBER	LENGTH METERS [FEET]
TRD795ZBLK-05M	0.50 [1.64]
TRD795ZBLK-1M	1.0 [3.28]
TRD795ZBLK-2M	2.0 [6.56]
TRD795ZBLK-3M	3.0 [9.84]
TRD795ZBLK-5M	5.0 [16.41]
TRD795ZBLK-7.5M	7.5 [24.61]
TRD795ZBLK-10M	10.0 [32.81]
TRD795ZBLK-15M	15.0 [49.21]

NOTES:

1. LSZH CABLE CHARACTERISTICS:
 FLAME RATING: IEC 60332-1
 CORROSIVE GAS: IEC 60754
 SMOKE EMISSION: IEC 61034
2. LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
3. PLUG CONFORMS TO TIA-1096.
4. CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY B.ZHANG CHECKED BY SPAN APPROVED BY DGUTTADAURO	DATE 12/04/2020 12/04/2020 12/04/2020	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	
SIZE A CAGE CODE 43321 DWG. NO. TRD795ZBLK		SCALE: NONE CAD FILE: TRD795ZBLK.SLDDRW	REV. A