


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/12/2007	D.PARHAM
B	ECN#3240: ADDED 1, 2, 5 & 25 FT LENGTHS	03/20/2008	D.PARHAM
C	ECN 6416: NEW FORMAT, ADD WIRE MAP, REVISE BOOT LOGO, PACKAGING	09/21/2012	DFRISIELLO
D	ECN 11197: ADDED 2X STRAIN RELIED, PVC, CLEAR	06/28/2021	GUTTADAURO



NOTES:


MATERIAL:
 PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0
 CONTACTS: PHOSPHOR BRONZE
 CABLE JACKET: PVC
 JACKET COLOR: SEE SHEET 2
 STRAIN RELIEF: PVC, CLEAR



FINISH:
 PLUG CONTACTS: 50 μINCHES GOLD IN CONTACT AREA OVER 100 μINCHES NICKEL PLATE OVERALL

CABLE CHARACTERISTICS:
 UNSHIELDED TWISTED PAIR, CATEGORY 5E
 24 AWG STRANDED COPPER

MISCELLANEOUS:
 PLUG CONFORMS TO TIA-1096.
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C.
 CABLES TO BE TESTED FOR CONTINUITY.
 CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 LABEL MARKING TO BE BLACK TEXT ON WHITE BACKGROUND.


REGULATORY COMPLIANCE:
 EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY D.PARHAM CHECKED BY C.MCCORMICK APPROVED BY J.ROBERTS	01/12/2007 01/12/2007 01/12/2007	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION CAT 5e CROSS OVER CABLE	SIZE A
REF	SCALE: NONE	CAGE CODE 43321	ITEM NO. TRD815CR-B
		CAD FILE: TRD815CR-B.SLDDRW	REV. D
			SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815CRBLK-1	BLACK	1 [0.31]	TRD815CRBL-1	BLUE	1 [0.31]	TRD815CRY-1	YELLOW	1 [0.31]
TRD815CRBLK-2	BLACK	2 [0.61]	TRD815CRBL-2	BLUE	2 [0.61]	TRD815CRY-2	YELLOW	2 [0.61]
TRD815CRBLK-3	BLACK	3 [0.91]	TRD815CRBL-3	BLUE	3 [0.91]	TRD815CRY-3	YELLOW	3 [0.91]
TRD815CRBLK-5	BLACK	5 [1.52]	TRD815CRBL-5	BLUE	5 [1.52]	TRD815CRY-5	YELLOW	5 [1.52]
TRD815CRBLK-7	BLACK	7 [2.13]	TRD815CRBL-7	BLUE	7 [2.13]	TRD815CRY-7	YELLOW	7 [2.13]
TRD815CRBLK-10	BLACK	10 [3.05]	TRD815CRBL-10	BLUE	10 [3.05]	TRD815CRY-10	YELLOW	10 [3.05]
TRD815CRBLK-15	BLACK	15 [4.57]	TRD815CRBL-15	BLUE	15 [4.57]	TRD815CRY-15	YELLOW	15 [4.57]
TRD815CRBLK-25	BLACK	25 [7.62]	TRD815CRBL-25	BLUE	25 [7.62]	TRD815CRY-25	YELLOW	25 [7.62]
TRD815CRGR-1	GREEN	1 [0.31]	TRD815CRR-1	RED	1 [0.31]			
TRD815CRGR-2	GREEN	2 [0.61]	TRD815CRR-2	RED	2 [0.61]			
TRD815CRGR-3	GREEN	3 [0.91]	TRD815CRR-3	RED	3 [0.91]			
TRD815CRGR-5	GREEN	5 [1.52]	TRD815CRR-5	RED	5 [1.52]			
TRD815CRGR-7	GREEN	7 [2.13]	TRD815CRR-7	RED	7 [2.13]			
TRD815CRGR-10	GREEN	10 [3.05]	TRD815CRR-10	RED	10 [3.05]			
TRD815CRGR-15	GREEN	15 [4.57]	TRD815CRR-15	RED	15 [4.57]			
TRD815CRGR-25	GREEN	25 [7.62]	TRD815CRR-25	RED	25 [7.62]			

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY <p style="text-align: center;">TELECOM/MODULAR</p>			
PRODUCT DESCRIPTION <p style="text-align: center;">CAT 5e CROSS OVER CABLE</p>			
SIZE A	CAGE CODE 43321	ITEM NO. TRD815CR-B	REV. D
SCALE: NONE		CAD FILE: TRD815CR-B.SLDDRW	
			SHEET 2 OF 2