


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/25/11	D.GRIFFIN
B	ECN6552: ADDED CHANNEL RATING NOTE	2/15/13	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/12/14	D.FRISIELLO



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	10/21/2011		CATEGORY TELECOM/MODULAR
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	CHECKED BY D. CASTRO	10/21/2011	PRODUCT DESCRIPTION C5E PVC UTP RGT-RGT	
PROJECTION 	D. GALLAGHER	10/24/2011	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRD815RA14
			CAD FILE: TRD815RA14.SLDDRW	REV. C
				SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815RA14BLK-1	BLACK	1.0 [0.30]	TRD815RA14RD-1	RED	1.0 [0.30]	TRD815RA14GRY-1	GRAY	1.0 [0.30]	TRD815RA14Y-1	YELLOW	1.0 [0.30]
TRD815RA14BLK-2	BLACK	2.0 [0.61]	TRD815RA14RD-2	RED	2.0 [0.61]	TRD815RA14GRY-2	GRAY	2.0 [0.61]	TRD815RA14Y-2	YELLOW	2.0 [0.61]
TRD815RA14BLK-3	BLACK	3.0 [0.91]	TRD815RA14RD-3	RED	3.0 [0.91]	TRD815RA14GRY-3	GRAY	3.0 [0.91]	TRD815RA14Y-3	YELLOW	3.0 [0.91]
TRD815RA14BLK-5	BLACK	5.0 [1.52]	TRD815RA14RD-5	RED	5.0 [1.52]	TRD815RA14GRY-5	GRAY	5.0 [1.52]	TRD815RA14Y-5	YELLOW	5.0 [1.52]
TRD815RA14BLK-7	BLACK	7.0 [2.13]	TRD815RA14RD-7	RED	7.0 [2.13]	TRD815RA14GRY-7	GRAY	7.0 [2.13]	TRD815RA14Y-7	YELLOW	7.0 [2.13]
TRD815RA14BLK-10	BLACK	10.0 [3.05]	TRD815RA14RD-10	RED	10.0 [3.05]	TRD815RA14GRY-10	GRAY	10.0 [3.05]	TRD815RA14Y-10	YELLOW	10.0 [3.05]
TRD815RA14BLK-15	BLACK	15.0 [4.57]	TRD815RA14RD-15	RED	15.0 [4.57]	TRD815RA14GRY-15	GRAY	15.0 [4.57]	TRD815RA14Y-15	YELLOW	15.0 [4.57]
TRD815RA14BLK-20	BLACK	20.0 [6.10]	TRD815RA14RD-20	RED	20.0 [6.10]	TRD815RA14GRY-20	GRAY	20.0 [6.10]	TRD815RA14Y-20	YELLOW	20.0 [6.10]
TRD815RA14BLK-25	BLACK	25.0 [7.62]	TRD815RA14RD-25	RED	25.0 [7.62]	TRD815RA14GRY-25	GRAY	25.0 [7.62]	TRD815RA14Y-25	YELLOW	25.0 [7.62]
TRD815RA14BLK-30	BLACK	30.0 [9.14]	TRD815RA14RD-30	RED	30.0 [9.14]	TRD815RA14GRY-30	GRAY	30.0 [9.14]	TRD815RA14Y-30	YELLOW	30.0 [9.14]
TRD815RA14BL-1	BLUE	1.0 [0.30]	TRD815RA14GR-1	GREEN	1.0 [0.30]	TRD815RA14OR-1	ORANGE	1.0 [0.30]			
TRD815RA14BL-2	BLUE	2.0 [0.61]	TRD815RA14GR-2	GREEN	2.0 [0.61]	TRD815RA14OR-2	ORANGE	2.0 [0.61]			
TRD815RA14BL-3	BLUE	3.0 [0.91]	TRD815RA14GR-3	GREEN	3.0 [0.91]	TRD815RA14OR-3	ORANGE	3.0 [0.91]			
TRD815RA14BL-5	BLUE	5.0 [1.52]	TRD815RA14GR-5	GREEN	5.0 [1.52]	TRD815RA14OR-5	ORANGE	5.0 [1.52]			
TRD815RA14BL-7	BLUE	7.0 [2.13]	TRD815RA14GR-7	GREEN	7.0 [2.13]	TRD815RA14OR-7	ORANGE	7.0 [2.13]			
TRD815RA14BL-10	BLUE	10.0 [3.05]	TRD815RA14GR-10	GREEN	10.0 [3.05]	TRD815RA14OR-10	ORANGE	10.0 [3.05]			
TRD815RA14BL-15	BLUE	15.0 [4.57]	TRD815RA14GR-15	GREEN	15.0 [4.57]	TRD815RA14OR-15	ORANGE	15.0 [4.57]			
TRD815RA14BL-20	BLUE	20.0 [6.10]	TRD815RA14GR-20	GREEN	20.0 [6.10]	TRD815RA14OR-20	ORANGE	20.0 [6.10]			
TRD815RA14BL-25	BLUE	25.0 [7.62]	TRD815RA14GR-25	GREEN	25.0 [7.62]	TRD815RA14OR-25	ORANGE	25.0 [7.62]			
TRD815RA14BL-30	BLUE	30.0 [9.14]	TRD815RA14GR-30	GREEN	30.0 [9.14]	TRD815RA14OR-30	ORANGE	30.0 [9.14]			

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C5E PVC UTP RGT-RGT			
SIZE A	FSCM NO. 43321	DWG. NO. TRD815RA14	REV. C
SCALE: NONE		CAD FILE: TRD815RA14.SLDDRW	
			SHEET 2 OF 2