



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/7/12	D.GRIFFIN
B	ECN6549: ADDED CHANNEL RATING NOTE	2/11/13	D. DESJARDIN
C	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	11/18/14	D.FRISIELLO



- NOTES:**
1. PLUG CONFORMS TO TIA-1096
  2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**  
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	3/2/12		CATEGORY TELECOM/MODULAR
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY J. RUST	3/6/12	PRODUCT DESCRIPTION C5E PVC FTP LFT-RGT	
PROJECTION 	APPROVED BY D. GALLAGHER	3/6/12	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>
			DWG. NO. TRD815SRA8	REV. <b>C</b>
			SCALE: NONE	CAD FILE: TRD815SRA8.SLDDRW
				SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815SRA8BLK-1	BLACK	1.0 [0.30]	TRD815SRA8RD-1	RED	1.0 [0.30]	TRD815SRA8GRY-1	GRAY	1.0 [0.30]	TRD815SRA8Y-1	YELLOW	1.0 [0.30]
TRD815SRA8BLK-2	BLACK	2.0 [0.61]	TRD815SRA8RD-2	RED	2.0 [0.61]	TRD815SRA8GRY-2	GRAY	2.0 [0.61]	TRD815SRA8Y-2	YELLOW	2.0 [0.61]
TRD815SRA8BLK-3	BLACK	3.0 [0.91]	TRD815SRA8RD-3	RED	3.0 [0.91]	TRD815SRA8GRY-3	GRAY	3.0 [0.91]	TRD815SRA8Y-3	YELLOW	3.0 [0.91]
TRD815SRA8BLK-5	BLACK	5.0 [1.52]	TRD815SRA8RD-5	RED	5.0 [1.52]	TRD815SRA8GRY-5	GRAY	5.0 [1.52]	TRD815SRA8Y-5	YELLOW	5.0 [1.52]
TRD815SRA8BLK-7	BLACK	7.0 [2.13]	TRD815SRA8RD-7	RED	7.0 [2.13]	TRD815SRA8GRY-7	GRAY	7.0 [2.13]	TRD815SRA8Y-7	YELLOW	7.0 [2.13]
TRD815SRA8BLK-10	BLACK	10.0 [3.05]	TRD815SRA8RD-10	RED	10.0 [3.05]	TRD815SRA8GRY-10	GRAY	10.0 [3.05]	TRD815SRA8Y-10	YELLOW	10.0 [3.05]
TRD815SRA8BLK-15	BLACK	15.0 [4.57]	TRD815SRA8RD-15	RED	15.0 [4.57]	TRD815SRA8GRY-15	GRAY	15.0 [4.57]	TRD815SRA8Y-15	YELLOW	15.0 [4.57]
TRD815SRA8BLK-20	BLACK	20.0 [6.10]	TRD815SRA8RD-20	RED	20.0 [6.10]	TRD815SRA8GRY-20	GRAY	20.0 [6.10]	TRD815SRA8Y-20	YELLOW	20.0 [6.10]
TRD815SRA8BLK-25	BLACK	25.0 [7.62]	TRD815SRA8RD-25	RED	25.0 [7.62]	TRD815SRA8GRY-25	GRAY	25.0 [7.62]	TRD815SRA8Y-25	YELLOW	25.0 [7.62]
TRD815SRA8BLK-30	BLACK	30.0 [9.14]	TRD815SRA8RD-30	RED	30.0 [9.14]	TRD815SRA8GRY-30	GRAY	30.0 [9.14]	TRD815SRA8Y-30	YELLOW	30.0 [9.14]
TRD815SRA8BL-1	BLUE	1.0 [0.30]	TRD815SRA8GR-1	GREEN	1.0 [0.30]	TRD815SRA8OR-1	ORANGE	1.0 [0.30]			
TRD815SRA8BL-2	BLUE	2.0 [0.61]	TRD815SRA8GR-2	GREEN	2.0 [0.61]	TRD815SRA8OR-2	ORANGE	2.0 [0.61]			
TRD815SRA8BL-3	BLUE	3.0 [0.91]	TRD815SRA8GR-3	GREEN	3.0 [0.91]	TRD815SRA8OR-3	ORANGE	3.0 [0.91]			
TRD815SRA8BL-5	BLUE	5.0 [1.52]	TRD815SRA8GR-5	GREEN	5.0 [1.52]	TRD815SRA8OR-5	ORANGE	5.0 [1.52]			
TRD815SRA8BL-7	BLUE	7.0 [2.13]	TRD815SRA8GR-7	GREEN	7.0 [2.13]	TRD815SRA8OR-7	ORANGE	7.0 [2.13]			
TRD815SRA8BL-10	BLUE	10.0 [3.05]	TRD815SRA8GR-10	GREEN	10.0 [3.05]	TRD815SRA8OR-10	ORANGE	10.0 [3.05]			
TRD815SRA8BL-15	BLUE	15.0 [4.57]	TRD815SRA8GR-15	GREEN	15.0 [4.57]	TRD815SRA8OR-15	ORANGE	15.0 [4.57]			
TRD815SRA8BL-20	BLUE	20.0 [6.10]	TRD815SRA8GR-20	GREEN	20.0 [6.10]	TRD815SRA8OR-20	ORANGE	20.0 [6.10]			
TRD815SRA8BL-25	BLUE	25.0 [7.62]	TRD815SRA8GR-25	GREEN	25.0 [7.62]	TRD815SRA8OR-25	ORANGE	25.0 [7.62]			
TRD815SRA8BL-30	BLUE	30.0 [9.14]	TRD815SRA8GR-30	GREEN	30.0 [9.14]	TRD815SRA8OR-30	ORANGE	30.0 [9.14]			

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY <b>TELECOM/MODULAR</b>			
PRODUCT DESCRIPTION <b>C5E PVC FTP LFT-RGT</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>TRD815SRA8</b>	REV. <b>C</b>
SCALE: NONE   CAD FILE: TRD815SRA8.SLDDRW			SHEET 2 OF 2