


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/12	D.FRISIELLO
B	ECN 6202: CHANGED BOOTS TO "PE"	6/7/12	D.DESJARDIN
C	ECN6553: UPDATED NOTES. CHANGED PE NOTE TO LSZH	1/14/13	D.DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	12/1/14	D.FRISIELLO



WIRING MAP

P1		P2
1	2	1 WHT/ORN
2	1	2 ORN
3	6	3 WHT/GRN
6	3	6 GRN
5	4	5 WHT/BLU
4	5	4 BLU
7	8	7 WHT/BRN
8	7	8 BRN
SHIELD		SHIELD

FOUR SHIELDED TWISTED PAIRS, CATEGORY 5E
 26 AWG STRANDED COPPER
 ALUMINUM/POLYESTER SHIELDING AND DRAIN WIRE
 LOW SMOKE ZERO HALOGEN JACKET
 SEE SHEET 2 FOR COLOR



NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	APPROVALS D.FRISIELLO CHECKED BY J.RUST APPROVED BY D. GALLAGHER	DATE 2/3/12 2/3/12 2/3/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. TRD815SZRA11		REV. D	SCALE: NONE CAD FILE: TRD815SZRA11.SLDDRW SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815SZRA11BLK-1	BLACK	1.0 [0.30]	TRD815SZRA11RD-1	RED	1.0 [0.30]	TRD815SZRA11GRY-1	GRAY	1.0 [0.30]
TRD815SZRA11BLK-2	BLACK	2.0 [0.61]	TRD815SZRA11RD-2	RED	2.0 [0.61]	TRD815SZRA11GRY-2	GRAY	2.0 [0.61]
TRD815SZRA11BLK-3	BLACK	3.0 [0.91]	TRD815SZRA11RD-3	RED	3.0 [0.91]	TRD815SZRA11GRY-3	GRAY	3.0 [0.91]
TRD815SZRA11BLK-5	BLACK	5.0 [1.52]	TRD815SZRA11RD-5	RED	5.0 [1.52]	TRD815SZRA11GRY-5	GRAY	5.0 [1.52]
TRD815SZRA11BLK-7	BLACK	7.0 [2.13]	TRD815SZRA11RD-7	RED	7.0 [2.13]	TRD815SZRA11GRY-7	GRAY	7.0 [2.13]
TRD815SZRA11BLK-10	BLACK	10.0 [3.05]	TRD815SZRA11RD-10	RED	10.0 [3.05]	TRD815SZRA11GRY-10	GRAY	10.0 [3.05]
TRD815SZRA11BLK-15	BLACK	15.0 [4.57]	TRD815SZRA11RD-15	RED	15.0 [4.57]	TRD815SZRA11GRY-15	GRAY	15.0 [4.57]
TRD815SZRA11BLK-20	BLACK	20.0 [6.10]	TRD815SZRA11RD-20	RED	20.0 [6.10]	TRD815SZRA11GRY-20	GRAY	20.0 [6.10]
TRD815SZRA11BLK-25	BLACK	25.0 [7.62]	TRD815SZRA11RD-25	RED	25.0 [7.62]	TRD815SZRA11GRY-25	GRAY	25.0 [7.62]
TRD815SZRA11BLK-30	BLACK	30.0 [9.14]	TRD815SZRA11RD-30	RED	30.0 [9.14]	TRD815SZRA11GRY-30	GRAY	30.0 [9.14]

L-com Global Connectivity
 45 BEECHWOOD DRIVE
 NORTH ANDOVER, MA
 01845

CATEGORY
TELECOM/MODULAR

PRODUCT DESCRIPTION
C5E LSZ FTP LFT-DWN

SIZE A	FSCM NO. 43321	DWG. NO. TRD815SZRA11	REV. D
------------------	--------------------------	--------------------------	------------------

SCALE: NONE | CAD FILE: TRD815SZRA11.SLDDRW | SHEET 2 OF 2