

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815SZRA2BLK-1	BLACK	1.0 [0.30]	TRD815SZRA2RD-1	RED	1.0 [0.30]	TRD815SZRA2GRY-1	GRAY	1.0 [0.30]
TRD815SZRA2BLK-2	BLACK	2.0 [0.61]	TRD815SZRA2RD-2	RED	2.0 [0.61]	TRD815SZRA2GRY-2	GRAY	2.0 [0.61]
TRD815SZRA2BLK-3	BLACK	3.0 [0.91]	TRD815SZRA2RD-3	RED	3.0 [0.91]	TRD815SZRA2GRY-3	GRAY	3.0 [0.91]
TRD815SZRA2BLK-5	BLACK	5.0 [1.52]	TRD815SZRA2RD-5	RED	5.0 [1.52]	TRD815SZRA2GRY-5	GRAY	5.0 [1.52]
TRD815SZRA2BLK-7	BLACK	7.0 [2.13]	TRD815SZRA2RD-7	RED	7.0 [2.13]	TRD815SZRA2GRY-7	GRAY	7.0 [2.13]
TRD815SZRA2BLK-10	BLACK	10.0 [3.05]	TRD815SZRA2RD-10	RED	10.0 [3.05]	TRD815SZRA2GRY-10	GRAY	10.0 [3.05]
TRD815SZRA2BLK-15	BLACK	15.0 [4.57]	TRD815SZRA2RD-15	RED	15.0 [4.57]	TRD815SZRA2GRY-15	GRAY	15.0 [4.57]
TRD815SZRA2BLK-20	BLACK	20.0 [6.10]	TRD815SZRA2RD-20	RED	20.0 [6.10]	TRD815SZRA2GRY-20	GRAY	20.0 [6.10]
TRD815SZRA2BLK-25	BLACK	25.0 [7.62]	TRD815SZRA2RD-25	RED	25.0 [7.62]	TRD815SZRA2GRY-25	GRAY	25.0 [7.62]
TRD815SZRA2BLK-30	BLACK	30.0 [9.14]	TRD815SZRA2RD-30	RED	30.0 [9.14]	TRD815SZRA2GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C5E LSZ FTP STR-UP			
SIZE A	FSCM NO. 43321	DWG. NO. TRD815SZRA2	REV. D
SCALE: NONE CAD FILE: TRD815SZRA2.SLDDRW			SHEET 2 OF 2