



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/9/12	D.FRISIELLO
B	ECN6202: CHANGED BOOTS FROM "LSZH" TO "PE". CHNGD TO SHIELDED PLUG	6/11/12	D.DESJARDIN
C	ECN6553: UPDATED NOTES. CHANGED PE NOTE TO LSZH	1/14/13	D.DESJARDIN
D	ECN 7667: REMOVE CHANNEL RATING NOTE AND ALL LENGTHS OVER 30 FT	12/1/14	D.FRISIELLO



- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
- REGULATORY COMPLIANCE:**
CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	APPROVALS D.FRISIELLO CHECKED BY J.RUST APPROVED BY D.GALLAGHER	DATE 2/3/12 2/3/12 2/3/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			CATEGORY TELECOM/MODULAR
	PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
	DWG. NO. TRD815SZRA8		SCALE: NONE	CAD FILE: TRD815SZRA8.SLDDRW
SHEET 1 OF 2		REV. D		

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815SZRA8BLK-1	BLACK	1.0 [0.30]	TRD815SZRA8RD-1	RED	1.0 [0.30]	TRD815SZRA8GRY-1	GRAY	1.0 [0.30]
TRD815SZRA8BLK-2	BLACK	2.0 [0.61]	TRD815SZRA8RD-2	RED	2.0 [0.61]	TRD815SZRA8GRY-2	GRAY	2.0 [0.61]
TRD815SZRA8BLK-3	BLACK	3.0 [0.91]	TRD815SZRA8RD-3	RED	3.0 [0.91]	TRD815SZRA8GRY-3	GRAY	3.0 [0.91]
TRD815SZRA8BLK-5	BLACK	5.0 [1.52]	TRD815SZRA8RD-5	RED	5.0 [1.52]	TRD815SZRA8GRY-5	GRAY	5.0 [1.52]
TRD815SZRA8BLK-7	BLACK	7.0 [2.13]	TRD815SZRA8RD-7	RED	7.0 [2.13]	TRD815SZRA8GRY-7	GRAY	7.0 [2.13]
TRD815SZRA8BLK-10	BLACK	10.0 [3.05]	TRD815SZRA8RD-10	RED	10.0 [3.05]	TRD815SZRA8GRY-10	GRAY	10.0 [3.05]
TRD815SZRA8BLK-15	BLACK	15.0 [4.57]	TRD815SZRA8RD-15	RED	15.0 [4.57]	TRD815SZRA8GRY-15	GRAY	15.0 [4.57]
TRD815SZRA8BLK-20	BLACK	20.0 [6.10]	TRD815SZRA8RD-20	RED	20.0 [6.10]	TRD815SZRA8GRY-20	GRAY	20.0 [6.10]
TRD815SZRA8BLK-25	BLACK	25.0 [7.62]	TRD815SZRA8RD-25	RED	25.0 [7.62]	TRD815SZRA8GRY-25	GRAY	25.0 [7.62]
TRD815SZRA8BLK-30	BLACK	30.0 [9.14]	TRD815SZRA8RD-30	RED	30.0 [9.14]	TRD815SZRA8GRY-30	GRAY	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY: TELECOM/MODULAR			
PRODUCT DESCRIPTION: C5E LSZ FTP LFT-RGT			
SIZE: A	FSCM NO.: 43321	DWG. NO.: TRD815SZRA8	REV.: D
SCALE: NONE CAD FILE: TRD815SZRA8.SLDDRW			SHEET 2 OF 2