


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 10806:ADD LSZH CABLE CHARACTERISTICS TO DWG, NEW FORMAT	11/25/2020	D.Guiffadauro




P1
RJ45 MODULAR
UNSHIELDED PLUG
GOLD PLATED CONTACTS
(8P8C)

P2
RJ45 MODULAR
UNSHIELDED PLUG
GOLD PLATED CONTACTS
(8P8C)

WIRING MAP





FOUR UNSHIELDED TWISTED PAIRS, CATEGORY 5E
24 AWG STRANDED COPPER
LOW SMOKE ZERO HALOGEN JACKET
SEE SHEET 2 OF 2 FOR COLOR

LSZH CABLE CHARACTERISTICS: 
FLAME RATING: IEC 60332-1
CORROSIVE GAS: IEC 60754
SMOKE EMISSION: IEC 61034


NOTES:

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936				
	DRAWN BY D.FRISIELLO	1/31/12		CATEGORY TELECOM/MODULAR			
	CHECKED BY J.RUST	1/31/12	PRODUCT DESCRIPTION C5E LSZ UTP RGT-RGT				
	APPROVED BY D. GALLAGHER	1/31/12	<table border="1"> <tr> <td>SIZE A</td> <td>CAGE CODE 43321</td> <td>ITEM NO. TRD815ZRA14</td> <td>REV. E</td> </tr> </table>	SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA14	REV. E
SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA14	REV. E				
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SCALE: NONE	CAD FILE: TRD815ZRA14.SLDDRW				

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRD815ZRA14BLK-1	BLACK	1.0 [0.30]	TRD815ZRA14RD-1	RED	1.0 [0.30]	TRD815ZRA14GRY-1	GRAY	1.0 [0.30]
TRD815ZRA14BLK-2	BLACK	2.0 [0.61]	TRD815ZRA14RD-2	RED	2.0 [0.61]	TRD815ZRA14GRY-2	GRAY	2.0 [0.61]
TRD815ZRA14BLK-3	BLACK	3.0 [0.91]	TRD815ZRA14RD-3	RED	3.0 [0.91]	TRD815ZRA14GRY-3	GRAY	3.0 [0.91]
TRD815ZRA14BLK-5	BLACK	5.0 [1.52]	TRD815ZRA14RD-5	RED	5.0 [1.52]	TRD815ZRA14GRY-5	GRAY	5.0 [1.52]
TRD815ZRA14BLK-7	BLACK	7.0 [2.13]	TRD815ZRA14RD-7	RED	7.0 [2.13]	TRD815ZRA14GRY-7	GRAY	7.0 [2.13]
TRD815ZRA14BLK-10	BLACK	10.0 [3.05]	TRD815ZRA14RD-10	RED	10.0 [3.05]	TRD815ZRA14GRY-10	GRAY	10.0 [3.05]
TRD815ZRA14BLK-15	BLACK	15.0 [4.57]	TRD815ZRA14RD-15	RED	15.0 [4.57]	TRD815ZRA14GRY-15	GRAY	15.0 [4.57]
TRD815ZRA14BLK-20	BLACK	20.0 [6.10]	TRD815ZRA14RD-20	RED	20.0 [6.10]	TRD815ZRA14GRY-20	GRAY	20.0 [6.10]
TRD815ZRA14BLK-25	BLACK	25.0 [7.62]	TRD815ZRA14RD-25	RED	25.0 [7.62]	TRD815ZRA14GRY-25	GRAY	25.0 [7.62]
TRD815ZRA14BLK-30	BLACK	30.0 [9.14]	TRD815ZRA14RD-30	RED	30.0 [9.14]	TRD815ZRA14GRY-30	GRAY	30.0 [9.14]

		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
CATEGORY <p style="text-align: center;">TELECOM/MODULAR</p>			
PRODUCT DESCRIPTION <p style="text-align: center;">C5E LSZ UTP RGT-RGT</p>			
SIZE A	CAGE CODE 43321	ITEM NO. TRD815ZRA14	REV. E
SCALE: NONE		CAD FILE: TRD815ZRA14.SLDDRW	
			SHEET 2 OF 2