



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/2018	DGUTTADAUR
B	ECN 9794:CBL JACKET CHANGED TO PVC,BLACK,OD WAS 5.8 MM,REM RoHS	04/24/2019	DGUTTADAUR



2X SNAGLESS BOOT WITH BOTH SIDES LOGO BLACK COLOR

HIGH FLEX, CAT5e CABLE  
 CONDUCTOR: FOUR TWISTED PAIR, 26AWG STRANDED BARE COPPER  
 SHIELD: TINNED COPPER BRAIDED  
 CABLE JACKET:PVC,BLACK COLOR,NOM. DIA .256 [6.50]  
 OPERATING TEMPERATURE RANGE: -40°C TO +80°C


POSITION 1



"P1"


2X RJ45 SHIELDED PLUG (8P8C) GOLD PLATED CONTACTS

POSITION 1



"P2"

**WIRING MAP**



PART NUMBER	LENGTH	
	FEET	METERS
TRD855HFB-05M	1.64	0.5
TRD855HFB-1M	3.28	1.0
TRD855HFB-2M	6.56	2.0
TRD855HFB-3M	9.84	3.0
TRD855HFB-4M	13.12	4.0
TRD855HFB-5M	16.41	5.0
TRD855HFB-10M	32.82	10.0

**NOTES**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY DCUI CHECKED BY SLI APPROVED BY SPAN	DATE 02/03/2018 02/03/2018 02/03/2018	50 HIGH STREET NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>TELCOM/MODULAR</b>
	PROJECTION 		PRODUCT DESCRIPTION <b>C5e RJ45 S/UTP 26STR PVC HIFLX BLK</b>
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b> FSCM NO. <b>43321</b> DWG. NO. TRD855HFB	REV. <b>B</b>

SCALE: NONE | CAD FILE: TRD855HFB.SLDDRW | SHEET 1 OF 1