



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/2018	DGUTTADAUR
B	ECN 9794:CBL JACKET CHANGED TO PVC,BLACK,OD WAS 5.8 MM,REM RoHS	04/24/2019	DGUTTADAUR



HIGH FLEX, CAT5e CABLE
 CONDUCTOR: FOUR TWISTED PAIR, 26AWG STRANDED BARE COPPER
 SHIELD: TINNED COPPER BRAIDED
 CABLE JACKET:PVC,BLACK COLOR,NOM. DIA .256 [6.50]
 OPERATING TEMPERATURE RANGE: -40°C TO +80°C

PART NUMBER	LENGTH	
	FEET	METERS
TRD855SRA6DBL-05M	1.64	0.5
TRD855SRA6DBL-1M	3.28	1.0
TRD855SRA6DBL-2M	6.56	2.0
TRD855SRA6DBL-3M	9.84	3.0
TRD855SRA6DBL-4M	13.12	4.0
TRD855SRA6DBL-5M	16.41	5.0
TRD855SRA6DBL-10M	32.82	10.0

- NOTES:**
1. PLUG CONFORMS TO TIA-1096
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE
	DRAWN BY DCUI	02/03/2018
	CHECKED BY SLI	02/03/2018
	APPROVED BY SPAN	02/03/2018
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
PROJECTION 	COLOR VARIATIONS MAY OCCUR	

L-com Global Connectivity		50 HIGH STREET NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION C5e RJ45 S/UTP STR-LFT 26STR PVC HIFLX BLK			
SIZE A	FSCM NO. 43321	DWG. NO. TRD855SRA6DBL	REV. B
SCALE: NONE		CAD FILE: TRD855SRA6DBL.SLDRW	SHEET 1 OF 1