





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	02/28/2018	DGUTTADAUR
B	ECN 9794:CBL JACKET CHANGED TO PVC,BLACK,OD WAS 5.8 MM,REM RoHS	04/24/2019	DGUTTADAUR




P2  
SHIELDED RJ45 MODULAR PLUG  
GOLD PLATED CONTACTS  
(8P8C)



HIGH FLEX, CAT5e CABLE  
CONDUCTOR: FOUR TWISTED PAIR, 26AWG STRANDED BARE COPPER  
SHIELD: TINNED COPPER BRAIDED  
CABLE JACKET:PVC,BLACK COLOR,NOM. DIA .256 [6.50]  
OPERATING TEMPERATURE RANGE: -40°C TO +80°C



PART NUMBER	LENGTH	
	FEET	METERS
TRD855SRA7DBL-05M	1.64	0.5
TRD855SRA7DBL-1M	3.28	1.0
TRD855SRA7DBL-2M	6.56	2.0
TRD855SRA7DBL-3M	9.84	3.0
TRD855SRA7DBL-4M	13.12	4.0
TRD855SRA7DBL-5M	16.41	5.0
TRD855SRA7DBL-10M	32.82	10.0



**NOTES:**

1. PLUG CONFORMS TO TIA-1096
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	DRAWN BY DCUI	02/03/2018
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.3]	CHECKED BY SLI	02/03/2018
PROJECTION	APPROVED BY SPAN	02/03/2018
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR	

**L-com** Global Connectivity  
50 HIGH STREET  
NORTH ANDOVER, MA  
01845

CATEGORY: TELECOM/MODULAR

PRODUCT DESCRIPTION: C5e RJ45 S/UTP STR-RGT 26STR PVC HIFLX BLK

SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRD855SRA7DBL	REV. <b>B</b>
------------------	--------------------------	---------------------------	------------------

SCALE: NONE | CAD FILE: TRD855SRA7DBL.SLDDRW | SHEET 1 OF 1