



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|--------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 9/4/14 | D. CASTRO |
| | | | |
| | | | |



HIGH FLEX, CAT 5e SHIELDED TWISTED PAIR 24AWG STRANDED TINNED COPPER WITH ALUM/POLY FOIL SHIELD AND TINNED COPPER BRAID. JACKET: THERMOPLASTIC ELASTOMER, BLACK (NOT SHOWN)



| MODEL NUMBER | LENGTH METERS [FEET] |
|--------------|----------------------|
| TRD8RGMT2-01 | 1.0 [3.28] |
| TRD8RGMT2-02 | 2.0 [6.56] |
| TRD8RGMT2-03 | 3.0 [9.84] |
| TRD8RGMT2-05 | 5.0 [16.41] |
| TRD8RGMT2-10 | 10.0 [32.81] |

NOTES:
 CRUSH RESISTANCE (1 IN SQ. AREA): 1500 POUNDS, MIN.
 TEMPERATURE RANGE: -40°C TO +80°C (-40°F TO +176°F)
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

| | | | |
|---|--|--|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 |
| | DRAWN BY D.FRISIELLO | 9/26/13 | |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [.51] .XXX = ±.005 [0.13] | CHECKED BY D.GUITADAURO | 9/26/13 | CATEGORY TELECOM/MODULAR |
| | APPROVED BY D.GALLAGHER | 9/26/13 | |
| PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | PRODUCT DESCRIPTION IP68 RGRJ45 P/P ANOD TPE | |
| | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 |
| | | DWG. NO. TRD8RGMT2 | REV. A |
| | | SCALE: NONE | CAD FILE: TRD8RGMT2.SLDDRW SHEET 1 OF 1 |