



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/1/11	D.GRIFFIN
-	-	-	-



PART NUMBER	LENGTH	
	FEET	[METERS]
TRDC6EXTF-3	3.0	[.91]
TRDC6EXTF-5	5.0	[1.52]
TRDC6EXTF-7	7.0	[2.13]
TRDC6EXTF-10	10.0	[3.05]
TRDC6EXTF-15	15.0	[4.57]
TRDC6EXTF-25	25.0	[7.62]

- NOTES:**
1. MODULAR CONNECTOR TO MEET TIA-1096.
  2. CABLE ASSEMBLY TO BE SHIPPED WITH (2) M3 X 10mm LONG PHILLIPS ROUND HEAD SCREWS
  3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] ≤+1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	1/25/11	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005	CHECKED BY D. PARHAM	1/26/11	PRODUCT DESCRIPTION CA C6 RJ45 M/F UTP FLANGED EXTENSION
PROJECTION 	APPROVED BY D. GALLAGHER	1/31/11	
REF	SCALE: NONE		CAD FILE: TRDC6EXTF.SLDRW SHEET 1 OF 1