



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/6/13	D.GRIFFIN
B	ECN 6765: CHANGED BULK CABLE FROM 24AWG TO 26AWG	4/2/13	D. DESJARDIN




- NOTES:
1. PLUG CONFORMS TO TIA-1096.
 2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. DESJARDIN	2/5/13		CATEGORY TELECOM/MODULAR
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005	CHECKED BY D. GUITADAURO	2/6/13	PRODUCT DESCRIPTION ECNMY RJ45/RJ45 CAT6	
PROJECTION 	APPROVED BY D. GALLAGHER	2/6/13	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. TRDE695
			CAD FILE: TRDE695.SLDDRW	SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRDE695BLK-3	BLACK	3.0 [0.91]	TRDE695RED-3	RED	3.0 [0.91]
TRDE695BLK-5	BLACK	5.0 [1.52]	TRDE695RED-5	RED	5.0 [1.52]
TRDE695BLK-7	BLACK	7.0 [2.13]	TRDE695RED-7	RED	7.0 [2.13]
TRDE695BLK-10	BLACK	10.0 [3.05]	TRDE695RED-10	RED	10.0 [3.05]
TRDE695BLK-14	BLACK	14.0 [4.27]	TRDE695RED-14	RED	14.0 [4.27]
TRDE695BLK-20	BLACK	20.0 [6.10]	TRDE695RED-20	RED	20.0 [6.10]
TRDE695BLK-25	BLACK	25.0 [7.62]	TRDE695RED-25	RED	25.0 [7.62]
TRDE695BLK-30	BLACK	30.0 [9.14]	TRDE695RED-30	RED	30.0 [9.14]
TRDE695GRY-3	GRAY	3.0 [0.91]	TRDE695BLU-3	BLUE	3.0 [0.91]
TRDE695GRY-5	GRAY	5.0 [1.52]	TRDE695BLU-5	BLUE	5.0 [1.52]
TRDE695GRY-7	GRAY	7.0 [2.13]	TRDE695BLU-7	BLUE	7.0 [2.13]
TRDE695GRY-10	GRAY	10.0 [3.05]	TRDE695BLU-10	BLUE	10.0 [3.05]
TRDE695GRY-14	GRAY	14.0 [4.27]	TRDE695BLU-14	BLUE	14.0 [4.27]
TRDE695GRY-20	GRAY	20.0 [6.10]	TRDE695BLU-20	BLUE	20.0 [6.10]
TRDE695GRY-25	GRAY	25.0 [7.62]	TRDE695BLU-25	BLUE	25.0 [7.62]
TRDE695GRY-30	GRAY	30.0 [9.14]	TRDE695BLU-30	BLUE	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY TELECOM/MODULAR			
PRODUCT DESCRIPTION ECNMY RJ45/RJ45 CAT6			
SIZE A	FSCM NO. 43321	DWG. NO. TRDE695	REV. B
SCALE: NONE		CAD FILE: TRDE695.SLDDRW	SHEET 2 OF 2