



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/4/11	D.GRIFFIN
B	ECN 6210: REMOVED L-COM LOGO, REMOVED EMPTY CHARTS	6/5/12	D.FRISIELLO
C	ECN 6765: CHANGED BULK CABLE FROM 24AWG TO 26AWG	4/2/13	D. DESJARDIN




- NOTES:
1. PLUG CONFORMS TO TIA-1096.
  2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D.FRISIELLO	10/26/11		CATEGORY TELECOM/MODULAR
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	CHECKED BY J.RUST	10/26/11	PRODUCT DESCRIPTION ECNMY RJ45/RJ45 CAT5E	
PROJECTION 	APPROVED BY D.GALLAGHER	10/26/11	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SCALE: NONE
	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. TRDE815
			CAD FILE: TRDE815.SLDDRW	SHEET 1 OF 2

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]
TRDE815BLK-3	BLACK	3.0 [0.91]	TRDE815RED-3	RED	3.0 [0.91]
TRDE815BLK-5	BLACK	5.0 [1.52]	TRDE815RED-5	RED	5.0 [1.52]
TRDE815BLK-7	BLACK	7.0 [2.13]	TRDE815RED-7	RED	7.0 [2.13]
TRDE815BLK-10	BLACK	10.0 [3.05]	TRDE815RED-10	RED	10.0 [3.05]
TRDE815BLK-14	BLACK	14.0 [4.27]	TRDE815RED-14	RED	14.0 [4.27]
TRDE815BLK-20	BLACK	20.0 [6.10]	TRDE815RED-20	RED	20.0 [6.10]
TRDE815BLK-25	BLACK	25.0 [7.62]	TRDE815RED-25	RED	25.0 [7.62]
TRDE815BLK-30	BLACK	30.0 [9.14]	TRDE815RED-30	RED	30.0 [9.14]
TRDE815GRY-3	GRAY	3.0 [0.91]	TRDE815BLU-3	BLUE	3.0 [0.91]
TRDE815GRY-5	GRAY	5.0 [1.52]	TRDE815BLU-5	BLUE	5.0 [1.52]
TRDE815GRY-7	GRAY	7.0 [2.13]	TRDE815BLU-7	BLUE	7.0 [2.13]
TRDE815GRY-10	GRAY	10.0 [3.05]	TRDE815BLU-10	BLUE	10.0 [3.05]
TRDE815GRY-14	GRAY	14.0 [4.27]	TRDE815BLU-14	BLUE	14.0 [4.27]
TRDE815GRY-20	GRAY	20.0 [6.10]	TRDE815BLU-20	BLUE	20.0 [6.10]
TRDE815GRY-25	GRAY	25.0 [7.62]	TRDE815BLU-25	BLUE	25.0 [7.62]
TRDE815GRY-30	GRAY	30.0 [9.14]	TRDE815BLU-30	BLUE	30.0 [9.14]

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY <b>TELECOM/MODULAR</b>			
PRODUCT DESCRIPTION <b>ECNMY RJ45/RJ45 CAT5E</b>			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>TRDE815</b>	REV. <b>C</b>
SCALE: NONE		CAD FILE: TRDE815.SLDDRW	SHEET 2 OF 2