


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/8/16	D.GRIFFIN



**NOTES:**

**MATERIAL:**

MOLDED HOOD: TPE, YELLOW  
 INSULATOR: PUR, BLACK  
 CONTACTS: COPPER ALLOY, GOLD OVER NICKEL PLATE  
 COUPLING NUT: BRASS, NICKEL PLATE  
 LABEL: PLASTIC FILM, BLACK/YELLOW

**ELECTRICAL:**

NOMINAL VOLTAGE RATING: 60VAC / 75VDC  
 MAX CURRENT: 4A

**APPLICATION:**

INGRESS PROTECTION RATING IS IP68 (MATED)

**ENVIRONMENTAL:**

OPERATING TEMPERATURE RANGE: -20°C TO +105°C

**MISCELLANEOUS:**

MINIMUM LABEL INFO INCLUDES PART NUMBER, DATE CODE, VOLTAGE AND AMPERAGE.  
 CABLE ASSEMBLIES TO BE TESTED FOR CONTINUITY  
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

WIRING MAP		
"P1"	COLOR	"J1"
1	BROWN	1
3	BLUE	3
4	BLACK	4

PART NUMBER	LENGTH METERS [FEET]
TRG317-C4Y-1M	1.0 [2.28]
TRG317-C4Y-2M	2.0 [6.56]
TRG317-C4Y-5M	5.0 [16.40]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3]	APPROVALS D.FRISIELLO CHECKED BY D.DESJARDIN APPROVED BY D.DESJARDIN	DATE 4/6/16 4/7/16 4/7/16	50 HIGH STREET NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION 3-POLE M8M-M8F PVC 24 YEL	
	PROJECTION 	SCALE: NONE	SIZE A	FSCM NO. 43321

REV. A