



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/14/2020	GUTTADAURO





"P1"
2X IP67 RJ45 PLUG
CAT 6A SHIELDED KIT

"P2"



MODEL NUMBER	LENGTH METERS [FEET]
TRG695AHF2-05M	0.5 [1.64]
TRG695AHF2-1M	1.0 [3.28]
TRG695AHF2-2M	2.0 [6.56]
TRG695AHF2-3M	3.0 [9.84]
TRG695AHF2-5M	5.0 [16.41]
TRG695AHF2-10M	10.0 [32.81]

- NOTES:**
- OIL AND UV RESISTANT CABLE IS SUITABLE FOR OUTDOOR OR INDUSTRIAL APPLICATIONS.
 - "P1" AND "P2" ARE IP-67 RATED WHEN MATED SECURELY.
 - CONNECTOR TEMPERATURE RATING: -40° C TO +68° C
CABLE TEMPERATURE RATING: -40° C TO +75° C
 - LENGTHS OVER 10 METERS (32.8 FT) ARE CHANNEL RATED.
 - PLUG CONFORMS TO TIA-1096.
 - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY DFRISIELLO 01/13/2020	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVED BY GUTTADAURO 01/14/2020	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY TELECOM/MODULAR
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION IP67RJ45/IP67RJ45 C6A SF/UTP TPE TEL HFX	SCALE: NONE CAD FILE: TRG695AHF2.SLDDRW SHEET 1 OF 1
SIZE A	CAGE CODE 43321	ITEM NO. TRG695AHF2	REV. A