


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/19/2021	GUITADAURO

IX PIN #	COLOR	RJ45 PIN #
1	ORN/WHT	1
2	ORN	2
3		
4	BLU	4
5	BLU/WHT	5
6	GRN/WHT	3
7	GRN	6
8		
9	BRN/WHT	7
10	BRN	8
SHIELD	SHELL	SHELL

MODEL #	LENGTH		
	CM	M	(FT)
TRGIX605IN-TEL-20CM	20	(.2)	(.66)
TRGIX605IN-TEL-1M	(100)	1	(3.28)
TRGIX605IN-TEL-3M	(300)	3	(9.84)





NOTES:

CABLE CHARACTERISTICS:
 FLEX LIFE: 1 MILLION CYCLE TEST (10X CABLE O.D. MIN. RAD.)
 10 MILLION CYCLE TEST (20X CABLE O.D. MIN. RAD.)
 TEMPERATURE RATING: -40 °C TO +75 °C
 VOLTAGE RATING: 300 V
 POE COMPLIANT TO 70 METERS WHEN INSTALLED PER RECOMMENDATIONS IN TIA TSB-184.
 FLAME RATING: CMX/CM OUTDOOR
 CABLE JACKET IS WELD SPATTER, SUNLIGHT (UV) AND CUTTING/MACHINING OIL RESISTANT.

CAT6a, 4 TWISTED PR, 26AWG STRANDED TINNED COPPER WITH ALUM/POLY SHIELD (100%) OVER TINNED COPPER BRAID SHIELD (80%), JACKET: HIGH FLEX THERMOPLASTIC ELASTOMER, TEAL CABLE O.D.: 0.275" NOM.

- NOMINAL VOLTAGE: 50 V AC/ 60 V DC
- IX CONNECTORS CONFORM TO IEC STANDARD 61076-3-124
- THIS PRODUCT (TYPE A) IS DEFINED FOR 10/100 MBIT/S AND 1/10 GBIT/S ETHERNET COMMUNICATION.
- RJ45 CONTACTS: 50um GOLD PLATED
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY BPUCHASKI	03/19/2021	
CHECKED BY DFRISIELLO	03/19/2021	PRODUCT DESCRIPTION IXA-RJ45J, Cat6a SF/UTP Hi-Flex CMX TPE TEL	
APPROVED BY GUITADAURO	03/19/2021		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. TRGIX605IN-TEL
SCALE: NONE		CAD FILE: TRGIX605IN-TEL.SLDDRW	REV. A