

6

5


4

3

2

1

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	UPDATED PER ECO-13673	06/25/2024	HBAKKE	DGUST



NOTES:

PHYSICAL:

- CONDUCTOR TYPE: 22AWG, STRANDED TC.
- INSULATION: HDPE.
- CONDUCTOR DIA: 1.5 ± 0.05 mm.
- CONNECTOR: 50U" GOLD PLATED.
- MINIMUM AVERAGE CABLE THICKNESS: .026 [0.65].

ELECTRICAL:

- BANDWIDTH: 100 MHz.
- NOMINAL VOLTAGE RATING: 30 V.
- RESISTANCE: $7.08\Omega/100$ m (MAXIMUM).
- IMPEDANCE: 100Ω .
- CAPACITANCE: 5600 pf/100m.
- PROPAGATION DELAY: 545 ns/100m (MAXIMUM).
- DELAY SKEW: 45 ns/100m (MAXIMUM).
- PASS FLUKE DSX 8000 CHANNEL TEST.

ENVIRONMENTAL:

- INSTALLATION TEMPERATURE RANGE: 0°C TO $\sim 50^{\circ}\text{C}$
- OPERATING TEMPERATURE RANGE: -40°C TO $\sim 80^{\circ}\text{C}$

MISCELLANEOUS

- CABLE ASSEMBLY TO BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENTLY RELEASED VERSION).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

P1	WIRE MAP	P2
YELLOW 1	—————	1 YELLOW
ORANGE 2	—————	2 ORANGE
WHITE 3	—————	3 WHITE
BLUE 6	—————	6 BLUE
SHIELDED S	—————	S SHIELDED

ITEM NO	LENGTH [TOL.]	
	METERS [mm]	FEET [IN]
TRGPC506-05M	0.5 [+35/-15]	1.64 [+1.38/- .59]
TRGPC506-1M	1 [+35/-20]	3.28 [+1.38/- .79]
TRGPC506-2M	2 [+35/-30]	6.56 [+1.38/-1.18]
TRGPC506-3M	3 [+35/-30]	9.84 [+1.38/-1.18]
TRGPC506-5M	5 [±60]	16.40 [±2.36]
TRGPC506-10M	10 [±80]	32.81 [±3.15]

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
X = ±.2 [5] FRACTIONS
XX = ±.02 [0.5] ± 1/32
XXX = ±.005 [0.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
≤12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINIT[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE	SHEET
NONE	1 OF 1

DESCRIPTION
PROFINET C5e 2P RJ45 SF/UTP 22STR PUR GRN

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	43321	KGLEBOVA	TRGPC506	B

6

5

4

3

2

1