

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

	REVISIONS					
REV	DESCRIPTION	DATE	APPROVAL			
Α	INITIAL RELEASE	01/21/2021	GUTTADAURO			

## TSFC7-XXX-XXXF CONSISTS OF A CONTINUOUS LENGTH OF BULK CABLE





DIA: .042+/-.002[1.06+/-.05]

## NOTES:

1. CONSTRUCTION:
CONDUCTOR: 26 AWG STRANDED BARE COPPER
INSULATION MATERIAL: FOAMED-PE
PAIRS: COLOR CODED SINGLES TWISTED INTO PAIRS

SHIELD (PAIR): AN ALUMINUM POLYESTER FÖIL SHIELD, 25% OVERLAPPING (ALUMINUM OUTWARD)
OUTER SHIELD: TINNED COPPER BRAID, 60% COVERAGE
JACKET: PVC, COLOR SEE CHART

CABLE DIA: 0.236" CABLE DIA: 0.236" +/- .008 [6.0 +/- 0.20mm]

2. PHYSICAL PROPERTIES: OPERATING TEMPERATURE RATING: -10 ° C TO +80 ° C STORAGE TEMPERATURE RATING: -20 ° C TO +80 ° C FLAME TEST:IEC60332-1

3. ELECTRICAL CHARACTERISTICS: VOLTAGE RATING: 30V DIELECTRIC STRENGTH: 500VAC/MINUTE

INSULATION RESISTANCE(FOAMED-PE):10MΩ-10m Min. AT 20 ° C

CONDUCTOR RESISTANCE(26AWG): 150Ω/KM Max. AT 20 ° C

4. ENVIRONMENT PROTECT STANDARD: RoHS2.0 and REACH COMPLIANT

5. JACKET PRINT(WHITE INK ON BLACK JACKET, BLACK INK ON BLUE JACKET): L-COM,INC WWW.L-COM.COM CAT.7 4PR 26AWG S/FTP PATCH CABLE PVC ROHS WW/YY

6. PACKAGE:

MODEL NUMBER	LENGTH	JACKET COLOR	PACKAGING	
TSFC7-BLK-1000F	1000.0 FT	BLACK (RAL9005)	SPOOL	
TSFC7-BLK-100F	100.0 FT	BLACK (RAL9005)	POLY BAG	
TSFC7-BLK-500F	500.0 FT	BLACK (RAL9005)	SPOOL	
TSFC7-BLU-1000F	1000.0FT	BLUE (RAL5017)	SPOOL	
TSFC7-BLU-100F	100.0 FT	BLUE (RAL5017)	POLY BAG	
TSFC7-BLU-500F	500.0FT	BLUE (RAL5017)	SPOOL	

	APPROVALS	DATE						
UNLESS OTHERWISE SPECIFIED,	DRAWN BY				50 HIGH STREET			
DIMENSIONS ARE IN INCHES [mm]	B.ZHANG	12/14/2020					NORTH ANI	
OVERALL CABLE LENGTH TOLERANCE:	CHECKED BY		an INFI		NIT brand	018	345	
S12 [305] = +1 [25] / -0	GUTTADAURO	12/14/2020	CATEGORY					
>12 [305] - 60 [1524] = +2 [51] / -0	APPROVED BY GUTTADAURO	12/14/2020	TELECOM/MODULAR					
>60 [1524] - 120 [3048] = +4 [102] / -0 >120[3048] - 300[7620] = +6 [152] / -0 >300[7620] = +5% / -0%								
>300[7620] = +5% / -0%	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION					
ALL OTHER DIMENSIONAL TOLERANCES:								
.X = .2 [5.08] .XX = .02 [.51]			CAT7 S/FTP 4PR/26 STR PVC JKT					
.XXX = .005 [.13]								
PROJECTION I	COLOR VARIATIONS MAY OCCUR		SIZE	FSCA	A NO.	DWG. NO.		REV.
			Α	433	321		TSFC7	A
				700				/ / \
Ψ —			SCALE	: NONE	CADF	ILE: TSFC7.SLDDR	W	SHEET 1 OF 1