



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	05/18/18	S.LI



**NOTES:**

- CABLE: [32AWG\*1P+EAM]\*4C+32AWG\*1P+32AWG\*4C+23AWG\*1C]+2EAB, OD: 4.8mm, BRAID:85%, JACKET: PVC, BLACK
- ELECTRICAL TEST:
  - 100% OPEN SHORT & MISS WIRE TEST
  - HI-POT: 100V AC/0.1S
  - INSULATION: 10M OHM MIN. AT 100V DC
  - CONDUCTOR RESISTANCE: 3 OHM MAX.

**PACKAGING:**  
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE 2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS S.LI	DATE 05/18/18	50 HIGH STREET NORTH ANDOVER, MA 01845			
	CHECKED BY B.ZHANG	DATE 05/18/18		CATEGORY USB		
	APPROVED BY B.GATES	DATE 05/18/18	PRODUCT DESCRIPTION CA, USB 3.1 TYPE C GEN2 M/M 10Gbps			
	PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. U1A00002
SCALE: NONE		CAD FILE: U1A00002.SLDDRW		SHEET 1 OF 1		