



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/15/2018	DFRISIELLO



**NOTES:**

- CABLE: [32AWG\*1P+EAM]\*4C+32AWG\*1P+32AWG\*4C+23AWG\*1C]+2EAB, OD: 4.8mm, BRAID:85%, JACKET: LOW SMOKE ZERO HALOGEN, BLACK
- ELECTRICAL TEST:
  - 100% OPEN SHORT & MISS WIRE TEST
  - HI-POT: 100V AC/0.1S
  - INSULATION: 10M OHM MIN. AT 100V DC
  - CONDUCTOR RESISTANCE: 3 OHM MAX.

**PACKAGING:**  
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
CE 2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $>12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $>60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $>120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $>300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	APPROVALS DRAWN BY DFRISIELLO	DATE 08/15/2018	50 HIGH STREET NORTH ANDOVER, MA 01845		
	CHECKED BY BGATES	DATE 08/15/2018		CATEGORY USB 3.1	
	APPROVED BY BGATES	DATE 08/15/2018		PRODUCT DESCRIPTION USB 3.1 LSZH Type C Gen 2 M/M 10Gbps	
	PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	FSCM NO. <b>43321</b>
SCALE: NONE			CAD FILE: U1A00003.SLDDRW	SHEET 1 OF 1	