



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/22/17	J.LABOY
B	ECN 9466: P1 END ADDED USB2.0 AM MODEL	10/18/18	B.GATES
C	ECN 10577 : UPD MODEL/DWG PER EXISTING PROD. UPD PROD DESCR., REMOVED -5M LENGTH	07/13/20	D.GUITADAURC



ONE 28AWG STRANDED TINNED COPPER TWISTED PAIR
 TWO 24AWG STRANDED TINNED COPPER CONDUCTORS
 OVERALL ALUMINIZED POLYESTER SHIELD WITH DRAIN WIRE
 PLUS TINNED COPPER BRAIDED SHIELD.
 PVC OUTER JACKET (UV RESISTANCE), BLACK (NOM DIA 4.5mm)



PART NUMBER	LENGTH	
	METERS	FEET
U2A00009-05M	0.5	1.64
U2A00009-1M	1.0	3.28
U2A00009-2M	2.0	6.56
U2A00009-3M	3.0	9.84

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY
2. WATERPROOF RATE: IP67 (ONLY P2 END WHEN MATED)
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [5] ANGLES ± 1° .XXX = ± .005 [13]	APPROVALS DRAWN BY D.CUI CHECKED BY B.ZHANG APPROVED BY B.GATES	DATE 06/21/17 06/21/17 06/22/17	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY USB 2.0	
THIRD-ANGLE PROJECTION	SIZE A	CAGE CODE 43321	DWG. NO. U2A00009
SCALE: NONE		CAD FILE: U2A00009.SLDDRW	REV. C SHEET 1 OF 1