


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/6/12	D.GRIFFIN
B	ECN 6064: UPDATED COMPATIBILITY NOTE TO WINDOWS 7 AND HIGHER	3/30/12	D. DESJARDIN



"J1"
USB TYPE A MALE
CONNECTOR

"J2"
DB9 MALE
CONNECTOR

FEATURES:

- FULL COMPLIANCE WITH USB VERSIONS 2.0 & 1.1
- SUPPORTS THE ASYNCHRONOUS SERIAL INTERFACES.
- OVER 1Mbps DATA TRANSFER RATE.
- COMPATIBLE WITH WINDOWS 98SE / ME / 2000 / XP / VISTA.
MAC OS 8.6 / OS-9 / OS-X, LINUX, WIN CE, WIN SERVER 2003, WIN SERVER 2008
AND WINDOWS 7 AND HIGHER.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY D.FRISIELLO	DATE 3/5/12	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D.PARHAM	3/5/12	
APPROVED BY S.SMITH	3/5/12	PRODUCT DESCRIPTION USB TO RS232 SERIAL CBL 1 MTR	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. UMC-201	REV. B
SCALE: NONE		CAD FILE: UMC-201.SLDDRW	SHEET 1 OF 1