


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/9/11	D.GRIFFIN



NOTES:

- MATERIAL: .06 THICK COLD ROLLED STEEL.
- FINISH: FLAT BLACK POWDER COAT.
- KIT INCLUDES (4) 6-32 UNC-2A PAN HEAD SCREWS.
- COUPLERS ARE SHIPPED WITH DUST CAPS INSTALLED. (NOT SHOWN)
- COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY D.FRISIELLO	DATE 8/4/11	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY M.SEDLESKI	DATE 8/4/11	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION USP SUB-PNL W/4 FC CPLR BLK	REV. A
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. USP4FOPT-FCB
SCALE: NONE		CAD FILE: USP4FOPT-FCB.SLDDRW	
SHEET 1 OF 1			SHEET 1 OF 1