


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|------------------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | REV A DRAWING RELEASED | 06/21/2018 | BPUCHASKI |
| | | | |
| | | | |



4X, CAT 6A KEYSTONE
RJ45/TL JACK
(L-COM P/N: RJTLC6A-POE)

NOTES:

1. PANEL MATERIAL: .06[1.5] THK COLD ROLLED STEEL.
2. PANEL FINISH: FLAT BLACK POWDER COAT.
3. KIT CONTAINS 4, #6-32 UNC SCREWS.
4. PACKAGE IN ACCORDANCE WITH L-COM SPEC. PS-0031

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)

| | | | | |
|--|--|------------|-------------------------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% | APPROVALS | DATE | | 50 HIGH STREET NORTH ANDOVER, MA 01845 |
| | DRAWN BY BPUCHASKI | 06/18/2018 | | CATEGORY |
| ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13] | CHECKED BY DFRISIELLO | 06/18/2018 | PRODUCT DESCRIPTION | |
| | APPROVED BY MMARTINEZ | 06/18/2018 | SUB PNL/4 C6A RJ45/110 POE JK | |
| PROJECTION | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | SIZE A | FSCM NO. 43321 |
| | COLOR VARIATIONS MAY OCCUR | | DWG. NO. USP4MK-C6A-POE | REV. A |
| | | | SCALE: NONE | CAD FILE: USP4MK-C6A-POE.SLDDRW |
| | | | SHEET 1 OF 1 | |