


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/09/2017	B.ZHANG
B	ECN 9020; REVISE NOTES TO REMOVE HDMI LABEL	12/22/2017	B.ZHANG

"P1"




2X, HDMI MALE  
19 PIN CONNECTOR  
GOLD PLATED CONTACTS

"P2"






PIN 1



2X, OVERMOLDED HOOD,  
PVC, RED(PANTONE 193C)

UL STYLE 20276, HIGH FLEX HDMI CABLE  
(5) INDIVIDUALLY SHIELDED TWISTED PAIRS, 28AWG, WITH DRAIN WIRE,  
(4) INDIVIDUAL CONDUCTORS, 28AWG,  
OVERALL SHIELD: ALUMINUM MYLAR PLUS BRAIDED TINNED COPPER,  
OUTER JACKET: PVC, BLACK  
(NOM. OD 7.3mm; CABLE IS RATED FOR 10,000 BEND CYCLES, MINIMUM)



PART NUMBER	LENGTH	
	METERS	FEET
VHA00001-05M	0.5	1.64
VHA00001-1M	1	3.28
VHA00001-2M	2	6.56
VHA00001-3M	3	9.84

**NOTES:**

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

**REGULATORY COMPLIANCE:**  
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: $\leq 12$ [305] = +1 [25] / -0 $> 12$ [305] $\leq 60$ [1524] = +2 [51] / -0 $> 60$ [1524] $\leq 120$ [3048] = +4 [102] / -0 $> 120$ [3048] $\leq 300$ [7620] = +6 [152] / -0 $> 300$ [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = $\pm .2$ [5.08] .XX = $\pm .02$ [51] .XXX = $\pm .005$ [13]	APPROVALS DRAWN BY B.ZHANG CHECKED BY B.GATES APPROVED BY S.PAN	DATE 05/04/2017 05/06/2017 05/06/2017	50 HIGH STREET NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>AUDIO/VIDEO</b>
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION <b>CA HDMI M-M, HI-FLEX</b>
	PROJECTION 	SIZE <b>A</b>	FSCM NO. <b>43321</b>
SCALE: NONE		CAD FILE: VHA00001.SLDDRW	REV. <b>B</b>