



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/26/2018	DFRISIELLO
B	ECN 9381: UPDATE PER VENDOR NEW SPEC SHEETS	08/29/2018	BGATES
C	ECN 9512: CHANGE DIM. 1.48 TO 1.89	11/14/2018	BPUGHASKI



WIRE MAP



NOTES:

ELECTRICAL:  
 VOLTAGE TEST: DC 300V 10ms  
 INSULATION RESISTANCE: 5.0M ohm/MIN.  
 CONDUCTOR RESISTANCE: 5.0 ohm/MAX.

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

REGULATORY COMPLIANCE:  
 CE2011/65/EU(RoHS DIRECTIVE)

MODEL NUMBER	LENGTH METERS [FEET]	TOLERANCE INCHES [MM]
VHA00012-05M	0.5 [1.64]	+1.0[25.0]/-0
VHA00012-1M	1.0 [3.28]	+2.0[51.0]/-0
VHA00012-2M	2.0 [6.56]	+2.0[51.0]/-0
VHA00012-3M	3.0 [9.84]	+4.0[102.0]/-0
VHA00012-4M	4.0[13.12]	+6.0[152.0]/-0

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845				
	DRAWN BY DFRISIELLO	01/23/2018					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY BGATES	01/26/2018	CATEGORY AUDIO/VIDEO				
	APPROVED BY BGATES	01/26/2018	PRODUCT DESCRIPTION HDMI FLAT CABLE MALE TO MALE				
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	<table border="1"> <tr> <td>SIZE <b>A</b></td> <td>FSCM NO. <b>43321</b></td> <td>DWG. NO. VHA00012</td> <td>REV. <b>C</b></td> </tr> </table>	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. VHA00012	REV. <b>C</b>
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. VHA00012	REV. <b>C</b>				
SCALE: NONE		CAD FILE: VHA00012.SLDDRW	SHEET 1 OF 1				