



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	REV A DRAWING RELEASED	01/03/2019	DCUI



MODEL NUMBER	LENGTH		TOLERANCE MM [INCHES]	CABLE O.D. NOM. DIA. MM [IN]
	METERS	FEET		
VHA00018-1M	1.0	3.28	30.0 [1.97]	6.0 [.236]
VHA00018-2M	2.0	6.56	50.0 [1.97]	6.0 [.236]
VHA00018-3M	3.0	9.84	80.0 [3.15]	7.3 [.287]
VHA00018-4M	4.0	13.12	80.0 [3.15]	7.3 [.287]

NOTES:
MATERIAL
 HOOD:PVC,UL94V-0
 DUSTPROOF:PVC
ELECTRIC TESTING
 INSULATION RESISTANCE:20MΩ MIN.
 CONDUCTOR RESISTANCE:3Ω MAX.
 VOLTAGE:300V DC/0.1S

ENVIRONMENTAL:
 INGRESS PROTECTION RATING IS IP67 (MATED,IEC60529:2001-02)
 OPERATING TEMPERATURE RANGE:-24°C TO 85°C
 HUMIDITY:10%~90%RH

MISCELLANEOUS
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 OVERALL CABLE LENGTH TOLERANCE:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤60 [1524] = +2 [51] / -0
 >60 [1524] ≤120 [3048] = +4 [102] / -0
 >120 [3048] ≤300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0%

ALL OTHER DIMENSIONAL TOLERANCES:
 .X = ± .2 [5.08]
 .XX = ± .02 [5.1]
 .XXX = ±.005 [1.3]

PROJECTION

APPROVALS	DATE
DRAWN BY DCUI	12/17/2018
CHECKED BY BZHANG	12/17/2018
APPROVED BY BGATES	12/17/2018

L-com Global Connectivity
 50 HIGH STREET
 NORTH ANDOVER, MA
 01845

CATEGORY: **AUDIO/VIDEO**

PRODUCT DESCRIPTION: **INDUSTRIAL HDMI AM TO AM W/DUST CAP**

SIZE A	FSCM NO. 43321	DWG. NO. VHA00018	REV. A
------------------	--------------------------	-----------------------------	------------------

SCALE: NONE | CAD FILE: VHA00018.SLDDRW | SHEET 1 OF 1