


Model 503

Small compact size clamp-meter that fits comfortably in a tool bag



Model 503
Jaw Opening: 1.1" (28mm)
Conductor Size: one 500kcmil cable



SPECIFICATIONS

MODEL	503
AC Current (Auto-Ranging)	0.05 to 400A
Resolution	0.01A and 0.1A
Accuracy	50 to 60Hz: ±1.5% of Reading ±10cts 60 to 500Hz: ±2.5% of Reading ±10cts
AC Voltage (Auto-Ranging)	0.5 to 600V
Resolution	0.1V and 1V
Accuracy	50 to 60Hz: ±0.8% of Reading ±5cts 60 to 500Hz: ±1.5% of Reading ±5cts
Input Impedance	10MΩ
DC Current (Auto-Ranging)	0.10 to 400A
Resolution	0.01A and 0.1A
Accuracy	±2.5% of Reading ±10cts
DC Voltage (Auto-Ranging)	0.2 to 600V
Resolution	0.1V and 1V
Accuracy	±1% of Reading ±2cts
Input Impedance	10MΩ
Resistance	0.2 to 400Ω
Accuracy	±1% of Reading ±2cts
Max Test Voltage	1.5Vdc
Continuity	<40Ω
Max Test Voltage	1.5Vdc
Power Source	Two 1.5V AAA batteries (included)

FEATURES

- Compact size - fits into your pocket
- 400A_{AC} or 400A_{AC/DC} current measurements
- 600V_{AC/DC} volts measurements
- Resistance measurements to 400Ω
- Continuity with beeper below 40Ω
- Hold function to “freeze” readings
- Push-button for easy A_{DC} zeroing
- Large, easy-to-read 4000-count LCD display
- 42-segment analog bargraph
- Includes test leads and soft carrying pouch

PRODUCT INCLUDES

Soft carrying case, set of two test leads, two 1.5V AAA batteries and user manual.



CATALOG NO.	DESCRIPTION
-------------	-------------

2117.22	Clamp-On Meter Model 503 (AC/DC, 400A _{AC/DC} , 600V _{AC/DC} , Ohms, Continuity)
---------	--