

Specifications

Electrical Specifications

Connectors	Self Sealing Screw Terminals
Clamping Voltage	+ or - 230 volts

Mechanical Specifications

Wire Gauge	26AWG (0.4mm) to 17AWG (1.2mm)
Overall insulation dia. of drop wire	0.2" (5mm) Dia. Maximum
Grounding	M4-0.7 Screw Terminal
RoHS Compliant	Yes

