




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES DHP9B-OD1	8/23/12	D.FRISIELLO



SPECIFICATIONS:

HOUSING: ABS PLASTIC, UL94V-0 RATED

COLOR: BLACK

HARDWARE SUPPLIED: FOUR 4-40 UNC-2A SCREWS,
TWO 4-40 UNC-2B HEX STANDOFFS,
FOUR PRESSURE PLATES.



HOUSING ACCEPTS STANDARD 9 POSITION D-SUB OR 15 POSITION,
HIGH DENSITY CONNECTORS (NOT SUPPLIED).

NOTES: HALF COVERS SNAP TOGETHER SECURELY, CAPTIVATING
D-SUB CONNECTORS.

COMPONENTS SHALL BE LOOSELY PACKAGED IN ACCORDANCE
WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D. PARHAM	5/29/2003		CATEGORY D-SUBMINIATURE		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ± .005 [1.27]	CHECKED BY C. MCCORMICK	6/2/2003	PRODUCT DESCRIPTION ADPT, COVER DB9 BLACK PLASTIC			
	APPROVED BY R. CARRICK	6/2/2003		<table border="1"> <tr> <td>SIZE A</td> <td>FSCM NO. 43321</td> <td>DWG. NO. DHP9B</td> <td>REV. A</td> </tr> </table>	SIZE A	FSCM NO. 43321
SIZE A	FSCM NO. 43321	DWG. NO. DHP9B	REV. A			
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SCALE: NONE CAD FILE: DHP9B.SLDDRW SHEET 1 OF 1			
COLOR VARIATIONS MAY OCCUR						