

TRS Jack RFI Cap With 3-Inch Stainless Steel Lanyard and .439-.443-Inch D-Ring



DSTCP-10-06305

Features

- Protects against dust and contaminants
- Protects against physical damage
- Nickel Plated Body
- Chain Included

Applications

- General Purpose Laboratory Use
- Test and Measurement

Description

The L-com's DSTCP-10-06305 is a TRS jack RFI cap with a 3-lug bayonet coupling design and a 3-inch stainless steel lanyard. The TRS jack RFI cap has a robust design and is easy to use. The TRS jack RFI cap is RoHS compliant.

The DSTCP-10-06305 RFI cap will keep your sensitive electronics protected from dust and other FOD. This TRS jack RFI cap is included .439-.443-inch d-ring to secure the cap in your assembly. The TRS jack RFI cap is suitable for applications such as aircraft avionics, test labs, the military/aero avionics market, and the avionics test market.

L-com has one of the largest in-stock selections of TRS jack RFI caps with same-day shipment. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the perfect TRS jack RFI cap for your requirements.

Mechanical Specifications

Configuration

Connector	
Chain Option	3 in Chain
Mating Cycles	500 Cycles

Description	Material	Plating
Body	Brass	Nickel
Coupling Nut	Brass	Nickel
Gasket	Silicone	
Chain	Stainless Steel	Nylon Jacket
Rivet	Brass	Nickel

Size

Length	4.4 in [111.76 mm]
Width	0.46 in [11.68 mm]
Height	0.46 in [11.68 mm]
Weight	0.01 lbs [4.54 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[TRS Jack RFI Cap With 3-Inch Stainless Steel Lanyard and .439-.443-Inch D-Ring DSTCP-10-06305](#)

TRS Jack RFI Cap With 3-Inch Stainless Steel Lanyard and .439-.443-Inch D-Ring



DSTCP-10-06305

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

TRS Jack RFI Cap With 3-Inch Stainless Steel Lanyard and .439-.443-Inch D-Ring from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

TRS Jack RFI Cap With 3-Inch Stainless Steel Lanyard and .439-.443-Inch D-Ring

L-com CAD Drawing

