

## 12x10x5 Inch Weatherproof NEMA 4X Enclosure With Blank Non-Metallic Starboard Mounting Plate

Model: NB121005-KIT01

### Applications and Features

---

**Features:**

- Molded Fiberglass Reinforced Polyester (FRP) industrial enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 4, 4X / IP66 rated
- Fully gasketed raised lid & integral mounting flange
- Includes blank, Non-Metallic Starboard Mounting Plate

**Applications:**

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage



### Product Description

---

The NB121005-KIT01 is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting feet allow the enclosure to be wall mounted as well as on a flat surface. The raised lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps. The raised lid is fully gasketed. The enclosure material is UV stabilized and comes in neutral gray color.

The NB121005-KIT01 includes a Blank Non-Metallic Starboard Mounting Plate permitting free form layout of equipment. The Enclosure and Mounting Plate combination is ideal for custom applications. Mounting stand-offs inside the enclosure are used to secure the Mounting Plate. The contoured body provides an attractive and contemporary appearance. The NB121005-KIT01 can be used as insulated communications box, terminal wiring box, instrument housing and housing for electrical controls in wet, dusty and corrosive environments.

Model: NB121005-KIT01


**Specifications**

<b>Enclosure Material</b>	Fiberglass Reinforced Polyester
<b>Enclosure Color</b>	Neutral Gray (RAL 7036)
<b>Weight</b>	6.3 lbs (2.85 kg)
<b>Outside Dimensions (max)</b>	13.31x11.31x5.59 inches (33.82x28.74x14.20 cm)
<b>Inside Dimensions</b>	12.00x10.00x4.84 inches (30.48x25.40x123.00 cm)
<b>Non-Metallic Mounting Plate, Blank</b>	12.00x9.13x0.250 inches 30.8x23.2x0.7 cm
<b>Flame Rating</b>	UL 94-5V
<b>RoHS Compliant</b>	Yes
<b>Ratings*</b>	NEMA Type 4, 4X / IP66

\*Note: Enclosure ports (Cable conduit connector and N-type holes for lightning protectors or connectors) must be properly sealed to maintain NEMA Type 4, 4X / IP66 rating.

**Enclosure and Mounting Plate Dimensions**

**NB121005 Enclosure**



Blank Non-Metallic Mounting Plate (.250 inches thick)

