

14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, 120-240 VAC Universal Outlet MNT PLT Vented Lid Black

# NBBPC141206-E0V



#### **Features**

- High-Impact, UV Resistant Polycarbonate (Black)
- · Stainless steel latches with padlock eye
- NEMA Type 3R / IP24 rated

#### **Applications**

- Remote Wireless LAN WiFi equipment installations
- · Indoor and outdoor installations
- Rapid Deployment Installations

- Fully gasketed vented lid with filters & user installed wall mounting brackets
- Features aluminum mounting plate with universal duplex socket for 120-240 VAC power
- · Corrosive environments & hotspot applications
- Protection of equipment from theft or damage

### **Description**

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from High-Impact, UV Resistant Polycarbonate material that provides superior durability to impacts and ease of modification while maintaining minimum weight. It is well suited for high temperature or corrosive environments. The lid includes two vents with installed rain guards and filters. The included wall mount brackets come uninstalled and bagged with their hardware inside of the enclosure. Once the brackets are installed the enclosure can be mounted directly to any flat wall surface provided proper screws are used into secure studs. The brackets, once installed, also allow you to use our HGX-PMT pole mount kits. The lid features a non-metallic hinge system that allows for quick removal & can be reattached just as quickly without the need for any tools. The enclosure comes with a pair of stainless-steel latches with padlock eyes allowing you to secure the enclosure from tampering. The enclosure comes in black.

#### Mounting Plate

The aluminum mounting plate included with the NBBPC141206-E0V features two 120-240 VAC Universal Euro outlets (contained in one duplex socket) and a terminal block for easy hook up to externally provided line power. The enclosure also features holes for two N-Bulkhead Lightning Protectors or Connectors, a grounding lug and cable conduit connector.

The HGX-PMT series of pole mounting kits allow the populated enclosure to be securely mounted to a variety of different size poles.

Compatible versions include HGX-PMT13, HGX-PMT16, HGX-PMT28, HGX-PMT29, HGX-PMT30, & HGX-PMT33

#### Size

oize		
Outer Height	14.6 in	[370.84 mm]
Outer Width	12.6 in	[320.04 mm]
Outer Depth	7.4 in	[187.96 mm]
Inner Height Inner Width Inner Depth	13.7 in 11.7 in 5.9 in	[347.98 mm] [297.18 mm] [149.86 mm]
Weight	8.85 lbs	[4.01 kg]

Enclosure Material Polycarbonate

## **Environmental Specifications**

Temperature Rating	-40° to 265°F [-40° to 129°C]
NEMA Rating	3R
Ingress Protection (IP) Rating	IP24

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, 120-240 VAC Universal Outlet MNT PLT Vented Lid Black NBBPC141206-



14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, 120-240 VAC Universal Outlet MNT PLT Vented Lid Black

# NBBPC141206-E0V



### **Compliance Certifications**

UL Listed No

14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, 120-240 VAC Universal Outlet MNT PLT Vented Lid Black from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components. Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, 120-240 VAC Universal Outlet MNT PLT Vented Lid Black NBBPC141206-E0V

URL: https://www.l-com.com/14x12x06-polycarbonate-weatherproof-outdoor-ip24-nema-3r-enclosure-120-240-vac-universal-outlet-mnt-plt-vented-lid-black-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

## **L-com CAD Drawing**

