


## 24x16x9 Inch Industrial Weatherproof Enclosure w/Blank Non-Metallic Mounting Plate Model: NBG241609-KIT01

### Applications

- Molded Fiberglass Reinforced Polyester (FRP) industrial Enclosure
- Stainless steel quick release latches with padlock hasps
- NEMA Type 4, 4X / IP66 rated
- Fully gasketed lid
- Includes blank non-metallic Starboard mounting plate

### Features

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage



## Description

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from molded fiberglass reinforced polyester, it is well suited for high temperature or corrosive environments. The mounting feet (optional) allow it to be wall mounted as well as on a flat surface. The lid features a stainless steel continuous hinge and stainless steel quick release latches with padlock hasps and is fully gasketed. The enclosure material is UV stabilized and comes in neutral grey color.

The NBG241609-KIT01 includes a Blank Non-Metallic Starboard Mounting Plate permitting free form layout of equipment. The Enclosure and Mounting Plate combination is ideal for custom applications. Mounting stand-offs inside the enclosure are used to secure the Mounting Plate. The contoured body provides an attractive and contemporary appearance. The NBG241609-KIT01 can be used as insulated communications box, terminal wiring box, instrument housing and housing for electrical controls in wet, dusty and corrosive environments.

## Specifications

<b>Enclosure Material</b>	Fiberglass Reinforced Polyester (FRP)
<b>Enclosure Color</b>	Neutral Grey (RAL 7032)
<b>Weight</b>	18.1 lbs (8.2 kg)
<b>Outside Dimensions</b>	24.21 x 16.34 x 9.06 in (615 x 415 x 230 mm)
<b>Inside Dimensions</b>	22.64 x 14.57 x 8.11 in (575 x 370 x 206 mm)
<b>Mounting Plate Material</b>	0.25 in. (6.3 mm) Thick Starboard Polypropylene
<b>Mounting Plate Dimensions</b>	21.65 x 13.78 in (550 x 350 mm)
<b>Flame Rating</b>	UL94-5V
<b>RoHS Compliant</b>	Yes
<b>Ratings</b>	NEMA Type 4, 4X / IP66