



an INFINIT® brand



# 14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, Modified Base Vented Lid Dark Gray

## NEMA Enclosures Technical Data Sheet

NBPC141206-03V

### Features

- High-Impact, UV Resistant Polycarbonate (Dark Gray)
- Stainless steel latches with padlock eye
- NEMA Type 3R / IP24 rated
- Fully gasketed vented lid & user installed wall mounting brackets
- Basic enclosure without mounting plate

### Applications

- Remote Wireless LAN WiFi equipment installations
- Indoor and outdoor installations
- Rapid Deployment Installations
- Corrosive environments & hotspot applications
- Protection of equipment from theft or damage

### Description

The box is a rugged weatherproof enclosure that is ideal for both indoor and outdoor applications. Constructed from High-Impact, UV Resistant Polycarbonate material that provides superior durability to impacts and ease of modification while maintaining minimum weight. It is well suited for high temperature or corrosive environments. The lid includes two vents with installed rain guards and filters. The included wall mount brackets come uninstalled and bagged with their hardware inside of the enclosure. Once the brackets are installed the enclosure can be mounted directly to any flat wall surface provided proper screws are used into secure studs. The brackets, once installed, also allow you to use our HGX-PMT pole mount kits. The lid features a non-metallic hinge system that allows for quick removal & can be reattached just as quickly without the need for any tools. The enclosure comes with a pair of stainless-steel latches with padlock eyes allowing you to secure the enclosure from tampering. The enclosure comes in a Dark Gray (Pantone 422C)

The HGX-PMT series of pole mounting kits allow the populated enclosure to be securely mounted to a variety of different size poles.

Compatible versions include HGX-PMT13, HGX-PMT16, HGX-PMT28, HGX-PMT29, HGX-PMT30, & HGX-PMT33

#### Size

|                    |               |             |
|--------------------|---------------|-------------|
| Outer Height       | 14.6 in       | [370.84 mm] |
| Outer Width        | 12.6 in       | [320.04 mm] |
| Outer Depth        | 7.4 in        | [187.96 mm] |
| Inner Height       | 13.7 in       | [347.98 mm] |
| Inner Width        | 11.7 in       | [297.18 mm] |
| Inner Depth        | 5.9 in        | [149.86 mm] |
| Weight             | 10.1 lbs      | [4.58 kg]   |
| Enclosure Material | Polycarbonate |             |

### Environmental Specifications

|                                |                                 |
|--------------------------------|---------------------------------|
| Temperature Rating             | -40° to 265° F [-40° to 129° C] |
| NEMA Rating                    | 3R                              |
| Ingress Protection (IP) Rating | IP24                            |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, Modified Base Vented Lid Dark Gray NB-PC141206-03V](#)



an INFINIT<sup>e</sup> brand

14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA  
3R Enclosure, Modified Base Vented Lid Dark Gray



## NEMA Enclosures Technical Data Sheet

**NBPC141206-03V**

### Compliance Certifications

UL Listed

No

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [14x12x06 Polycarbonate Weatherproof Outdoor IP24 NEMA 3R Enclosure, Modified Base Vented Lid Dark Gray NBPC141206-03V](https://www.l-com.com/nema-enclosures-14x12x06-polycarbonate-weatherproof-nema-3r-enclosure-modified-base-vented-lid-dark-gray-nbpc141206-03v)

URL: <https://www.l-com.com/nema-enclosures-14x12x06-polycarbonate-weatherproof-nema-3r-enclosure-modified-base-vented-lid-dark-gray-p.aspx>



