

Specifications

Input Voltage Range	12 VDC to 26 VDC
Output Current	0.8 Amps Max.
Output Voltage	48 VDC
Input Connection	Cigarette Plug with 28 in. (0.7m) Lead
Output Connection	2.5mm DC Plug (2.5mm x 5.5mm x 10mm), Center Positive with 72 in. (1.8m) Lead
Weight	0.9 lbs. (.40 kg)
Dimensions	4.1 x 2.6 x 1.4 (inches) 104 x 66 x 35 (mm)
RoHS Compliant	Yes