

Passive CWDM, Compact Demux, 4 channel, starting at 1551nm, 20 nm spacing, 900um 1m fiber, no connector w/ Express Port



PCWND-04355-19N3

Features

- Passive
- CWDM
- Compact Demux
- 4 channel
- Starting at 1551nm
- 20nm spacing
- 900um fiber 1m long with no connector
- Express Port

Applications

- Single Mode Fiber Networking
- Single Fiber
- Mux function
- Metro transport
- Regional Distribution
- Outside Plant (OSP) Operation

Description

L-com's PCWND-04355-19N3 is a CWDM passive filter with 8 channels. L-com's PCWND-04355-19N3 is a compact demultiplexer module starting at channel 1551nm. L-com's PCWND-04355-19N3 has 20nm spacing with 900um fiber lead which is 1m long and has no connector. L-com's PCWND-04355-19N3 has a express port designed for adding more wavelengths to the existing network. It is used by connecting the common (or line) port from another multiplexer utilizing different wavelengths. The addition of these channels allows for network expansion without interruption of existing connectivity, or additional fiber usage. L-com's PCWND-04355-19N3 is one of thousands of fiber optic products available in-stock and ready to ship today.

Configuration

Filter Type	CWDM
Module Type	Compact
Module Function	Mux/Demux
Number of Channels	4
Starting Channel	1551nm
Optional Ports	Express Port

Filter Specifications

Description	Minimum	Typical	Maximum	Units
Operating Wavelength	1260		1620	nm
Pass Band	-6.5		6.5	nm
Pass Band Ripple			0.5	dB
Channel Spacing (nm)		20		nm
Channel Insertion Loss			1	dB
Return Loss	45			dB
Directivity			45	dB
PDL			0.2	dB
PMD			0.2	PS
Power Handling			300	mW

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Passive CWDM, Compact Demux, 4 channel, starting at 1551nm, 20 nm spacing, 900um 1m fiber, no connector w/ Express Port PCWND-04355-19N3](#)

Passive CWDM, Compact Demux, 4 channel, starting at 1551nm,
20 nm spacing, 900um 1m fiber, no connector w/ Express Port

PCWND-04355-19N3



Size

Length	1.73 in [43.94 mm]
Weight	0.18 lbs [81.65 g]

Environmental Specifications

Temperature

Operating Range	-5 to +70 deg C
Storage Range	-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Passive CWDM, Compact Demux, 4 channel, starting at 1551nm, 20 nm spacing, 900um 1m fiber, no connector w/ Express Port from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Passive CWDM, Compact Demux, 4 channel, starting at 1551nm, 20 nm spacing, 900um 1m fiber, no connector w/ Express Port

L-com CAD Drawing

