

**Specifications:**

<b>Model: SC2403N</b>	
Type	3-Way
Frequency	2400 – 2500 MHz
Insertion Loss*:	≤ 0.5 dB; Ports 1 & 3
	≤ 0.7 dB; Port 2
VSWR	<1.5:1 Typical
Power Rating	25 Watts
Temperature Range	-40° C to +85° C
Dimensions (L x D x H)	4.6 x 2.6 x 1.7 (inches) 117 x 66 x 43 (mm)
Weight	0.65 lbs (0.29 kg)
Reverse Port Isolation	NO
RoHs Compliant	YES

\*Insertion loss figure excludes power division