

AAM1-1700 NMO Connector Mounting Instructions: For 3/4" (19mm) Hole



Step 1:

Drill 3/4" (19mm) Dia. hole in panel.

Note, max. panel thickness = 5/32" (4 mm)

Insert cable with NMO connector as shown.

Note, connector installs from top of panel.



Step 2:

Insert connector so that mounting flanges are underneath panel. (See next photo)



Step 3:

Move protective cover into place as shown.

(Photo shown from underneath panel)



Step 4:

Attach the top of the connector as shown.

Note: O-Ring should be facing panel for proper seal.



Before securing fully, inspect underneath panel to ensure connector is properly seated in mounting hole.