

## 4-Post Racks

**Available for Same-Day Shipping!**



The LCOM Adjustable 4-post Network Racks have an open frame that's designed for flexibility, allowing you to make the server rack choices that are right for your network build. Made from high quality materials, this product is made to industry specifications, ensuring compatibility with your equipment.

Model / SKU Number	LC4POST12U-M6	LC4POST18U-M6	LC4POST12U-12-24	LC4POST18U-12-24	LC4POST25U-12-24	LC4POST45U-12-24	
<b>PHYSICAL</b>							
Rack Capacity ( n Rack Units)	12U	18U	12U	18U	25U	45U	
Rack Depth (in) • adjustable in 1.5" increments	22-40	22-40	22-40	22-40	22-40	22-40	
Unit Dimensions (in)	H	26.7	37.21	29.7	40.2	49.5	84.53
	w	20.67	20.67	20.5	20.5	20.67	20.67
	D	22.5-40.7	22.5-40.7	22.4-38.4	22.4-38.4	22.5-40.7	22.5-40.7
Weight Capacity (kg/ lbs)	600   1322	600   1322	600   1322	600   1322	600   1322	600   1322	
Material	Cold Rolled Steel						
Painting/ Coating	Black Powder Coating						
Construction	Bolted Assembly						
Rack Hole Type	Square Holes		12-24 Threaded				
<b>ADDITIONAL FEATURES</b>							
Casters   Floor Mount	Includes Casters (Can also Floor Mount)		Includes Casters (Can also Floor Mount)		Floor Mount (Compatible with Casters)		
Cable Management	Includes Cable Hooks		Includes Cable Hooks				
Equipment Mounting Hardware	(20 Sets) M6 Cage Nuts, Screws, Plastic Washers		(20) 12-24 Screws				
Assembly	Assembly Required						
<b>COMPLIANCE AND CERTIFICATIONS</b>							
EIA/ECA 310-E	✓						
ROHS	✓						
CE	✓						
DIN 41494	✓						
IEC-60297-3-100	✓						
<b>SHIPPING</b>							
Shipping Dimensions (in)	L	28.15	42.1	28.3	42.35	50.5	85
	w	9.1	6.9	9.25	7.5	6	6
	H	5.7	5.5	6.3		6	6
Shipping Weight (lbs)	39.7	44	42.8	45.55	47.15	60.45	



