

**Bulk Cable Specification**

**FINISHED GOOD PART NUMBER**  
 CSLSZH09-100 100 FOOT COIL  
 CSLSZH09-500 500 FOOT SPOOL  
 CSLSZH09-1000 1000 FOOT SPOOL

**PRODUCTION PART NUMBER**  
 1AL08-033

<p><b>Cross-Sectional View</b></p>	<p><b>Color Code</b></p> <ol style="list-style-type: none"> <li>1. BLACK</li> <li>2. RED</li> <li>3. WHITE</li> <li>4. GREEN</li> <li>5. ORANGE</li> <li>6. BLUE</li> <li>7. WHITE / BLACK</li> <li>8. RED / BLACK</li> <li>9. GREEN / BLACK</li> </ol>
------------------------------------	---

No of Conductors		9
Conductor	Material	Stranded Tinned Copper
	Construction	24 AWG (7/32)
Insulation	Material	High Density Polyethylene
	Nominal Thickness	.012"
Shielding	Coverage	100% Coverage
	Material	Aluminum Polyester (foil facing out)
Drain Wire	Construction	24 AWG (7/32)
	Material	Stranded Tinned Copper
Braiding	Coverage	65% coverage (minimum)
	Material	36 AWG Tinned Copper Wire
Jacket	Nominal Thickness	.025"
	Nominal Diameter	.251"
	Material	Low Smoke Zero Halogen
	Color	Black

Minimum Marking: L-COM LOW SMOKE ZERO HALOGEN - 9/C 24 AWG IEC 332 PART 1 IEC 754 IEC 1034  
 – (lot designator)

**ELECTRICAL PROPERTIES**

DC Resistance	26.2 Ω/M'
DC Rating	30V (Min)
Capacitance	18.5pF / ft (mutual)
Dielectric Withstanding Voltage	1500 V rms
Temperature Rating (max)	60°C

Regulatory Compliance: CE2011/65/EU (RoHS DIRECTIVE)