




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/11/2021	MBLACKWOOD




C13 JACK  
EN60320  
BLACK



C14 PLUG  
EN60320  
RIGHT ANGLE  
BLACK

MODEL NO.	LENGTH +/-2%
PPA00020-3F	3.0 FEET
PPA00020-6F	6.0 FEET
PPA00020-10F	10.0 FEET

- NOTES:
1. APPROVALS: UL / CSA OR cUL
  2. RATING: 10A / 250V
  3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY DFRISIELLO CHECKED BY DZINN APPROVED BY MBLACKWOOD	DATE 01/11/2021  01/11/2021  01/11/2021	 an INFINITI brand  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY  COLOR VARIATIONS MAY OCCUR	CATEGORY  <b>POWER PRODUCTS</b>  PRODUCT DESCRIPTION <b>CPU/PDU Power Cord - C14 Right Angle to C13 - 10 Amp</b>	SIZE <b>A</b> CAGE CODE <b>43321</b> ITEM NO. PPA00020