


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES TDG1026-8R-OD1 AT REV A	11/13/14	D. CASTRO
.	.	.	.
.	.	.	.
.	.	.	.



WIRE MAP	
"J1"	"J2"
1	8
2	7
3	6
4	5
5	4
6	3
7	2
8	1

- NOTES:
- CROSS WIRED.
 - UL94V-0 FLAMMABILITY RATING.
 - JACK PIN PLATING: 15 MICROINCHES GOLD OVER NICKEL.
 - COMPONENT SHALL BE TESTED FOR CONTINUITY.
 - COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	APPROVALS DRAWN BY TJC CHECKED BY DFP APPROVED BY RC	DATE 10/3/01 10/4/01 10/9/01	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY TELECOM/MODULAR	PRODUCT DESCRIPTION MODULAR COUPLER 8X8 CROSSED
PROJECTION 	SIZE A	FSCM NO. 43321	DWG. NO. TDG1026-8R
		REV. A	