


D-SUBMINIATURE

Premium Lines:

CS2N, CS2NB, CS2H, CS2HB Series




FOR HIGH EMI/RFI APPLICATIONS

- Double shielded cable (foil + braid)
- 360° full metal shell around backshell
- Gold plated contacts
- Metal thumbscrews that can be hand tightened

Premium Lines:

CSMN, CSMNB, CHD Series




INDUSTRY STANDARD

- Shielded cable (foil)
- 360° copper foil shield around backshell
- Gold plated contacts
- Metal thumbscrews that can be hand tightened

Premium Lines:

CSM Series



OUR MOST ECONOMICAL SOLUTION

- Shielded cable (foil)
- 360° foil shield around backshell
- Gold flash contacts
- Slotted machine screws

USB

Premium line:

CSMU Series



FOR HIGH POWER APPLICATIONS

- 20 AWG power conductors for max current
- Double shielded cable (foil + braid)
- 30μ gold plated contacts

Deluxe Line:

CAUBLK Series



INDUSTRY STANDARD

- 24 AWG power conductors for medium current
- Double shielded cable (foil + braid)
- 30μ gold plated contacts

Economy Line:

ECUSB Series




OUR MOST ECONOMICAL SOLUTION

- 26 AWG power conductors
- Double shielded cable (foil + braid)
- 30μ gold plated contacts
- Eight off-the-shelf lengths

AUDIO/VIDEO

VGA



Premium Line: CTLF3VGA Series



FOR HIGH EMI/RFI APPLICATIONS

- Double shielded cable + steel box in backshell + molded ferrite cores for superior EMI/RFI protection

Deluxe Lines: CTL3VGA, CTL3VGA-B (black) Series



FOR MEDIUM EMI/RFI APPLICATIONS

- Double shielded cable + steel box in backshell for increased EMI/RFI protection
- 45° versions available

Economy Lines: CGSVGA Series



INDUSTRY STANDARD

- Double shielded cable
- 360° copper foil shield in backshell
- Off-the-shelf lengths from 3-50 feet

DVI

Premium Lines: CTLDVI, CTLDVI-DL Series

FOR HIGH EMI/RFI & PROFESSIONAL VIDEO APPLICATIONS

- 30μ gold plated contacts
- Angled versions available
- Ferrites for EMI/RFI protection
- Available in DVI-D and DVI-I variations



Deluxe Lines: CTLDVI, CTLDVI-DL Series

INDUSTRY STANDARD

- Gold flash contacts
- Ferrites for EMI/RFI protection
- Fully molded backshells provide excellent strain relief




AUDIO/VIDEO

HDMI

Premium Lines: HDCA Series

FOR PROFESSIONAL A/V APPLICATIONS


- Six colors available
- 30μ gold plated contacts
- Angled versions available
- Support for Ethernet




Deluxe Lines: CGHD Series

INDUSTRY STANDARD

- Gold flash contacts
- Support for Ethernet
- Seven off-the-shelf lengths from 0.3m to 5m



DIN AND MINI DIN



Premium Lines: DK226, DK238 Series

FOR HIGH EMI/RFI APPLICATIONS OR CARRYING POWER

- Double shielded cable (foil + braid)
- 24AWG conductors
- Gold plated contacts
- Available only from L-com off-the-shelf



Deluxe Lines: CSMD6, CSMD8 Series

INDUSTRY STANDARD

- Shielded cable (foil)
- 28AWG conductors
- Gold plated contacts

