


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	05/10/01	MCCORMICK
B	ECN 3112: UPDATE DWG FORMAT	12/14/07	D.GRIFFIN



NOTES:

MATERIAL:
 BODY - NICKEL PLATED ZINC ALLOY (DIE CAST)
 CENTER CONTACT - BRASS
 INSULATION - DELRIN

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]
 TOLERANCES TO BE:
 .X ±.1 [2.5] ANGLES ±2°
 .XX ±.01 [.25]
 .XXX ±.005 [.13]
 OVERALL CABLE LENGTH TOL:
 ≤ 60 [1524] +3 [76.2] / -0
 > 60 [1524] +5% / -0%

APPROVALS		DATE
DRAWN BY	MCCORMICK	05/01/01
CHECKED BY	D.PARHAM	05/10/01
APPROVED BY	R.CARRICK	05/10/01
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		

	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY COAXIAL	
PRODUCT DESCRIPTION BNC CONNECTORS AND ADAPTORS		
SIZE A	FSCM NO. 43321	DWG. NO. BA1087E
SCALE: NONE CAD FILE: BA1087E.SLDDRW		REV. B
SHEET 1 OF 1		