




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	08/02/01	McCORMICK
B	ECN4144: .92 WAS .9 AND .47 WAS .50. UPDATED FORMAT.	07/22/09	DFP
.	.	.	.
.	.	.	.



RoHS Compliant ✓

NOTES:

MATERIAL:
 BODY: NICKEL PLATED STEEL
 INSULATION: WHITE TEFLON
 CONTACTS ARE GOLD PLATED

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	APPROVALS DRAWN BY MCCORMICK	DATE 08/02/01	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CHECKED BY D.PARHAM APPROVED BY R.CARRICK	DATE 08/02/01 08/03/01	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION MINI UHF JACK TO SMA PLUG	
COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. BA582
REF	SCALE: NONE	CAD FILE: BA582.SLDDRW	REV. B
			SHEET 1 OF 1