


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	11/20/01	MCCORMICK
B	UPDATED DRAWING PER ECN# 1204	10/31/02	MCCORMICK
C	ECN 3134: UPDATE DWG FORMAT	12/31/07	D.GRIFFIN




NOTES:

**MATERIAL:**  
 BODY: BRASS  
 DIELECTRIC: DELRIN  
 CENTER PIN: BRASS

**FINISH:**  
 BODY: NICKEL PLATED  
 CENTER PIN: NICKEL PLATED

UNLESS OTHERWISE SPECIFIED,  
 DIMENSIONS ARE IN INCHES [mm]  
 TOLERANCES TO BE:  
 .X ±.1 [2.5] ANGLES ±2°  
 .XX ±.01 [.25]  
 .XXX ±.005 [.13]  
 OVERALL CABLE LENGTH TOL:  
 ≤ 60 [1524] +3 [76.2] / -0  
 > 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY MCCORMICK	11/20/01
CHECKED BY D.PARHAM	11/20/01
APPROVED BY R.CARRICK	11/20/01

CONFIGURATION DETAILS OF  
 UNDIMENSIONED FEATURES  
 MAY VARY

	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CATEGORY COAXIAL	
PRODUCT DESCRIPTION RCA JACK TO "F" JACK		
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>BA887</b>
SCALE: NONE   CAD FILE: BA887.SLDDRW		REV. <b>C</b>
SHEET 1 OF 1		